

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263492

Luminaire Tested: P3AS20R459727D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263492
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R459727D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R45 optic, 2700K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1582.0 lumens
Efficiency: N/A
Efficacy: 54.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263492

CATALOG NUMBER: P3AS20R459727D010 E3DL1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1263492

CATALOG NUMBER: P3AS20R459727D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	594097
5°	580166
10°	533323
15°	451898
20°	350614
25°	245095
30°	154404
35°	90882
40°	51439
45°	24995
50°	8699
55°	7034
60°	6842
65°	6590
70°	6347
75°	6015
80°	5304
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24995 cd/sqm

TEST NUMBER: P1263492

CATALOG NUMBER: P3AS20R459727D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.0	15.4
10°-20°	546.6	34.6
20°-30°	464.2	29.3
30°-40°	221.4	14.0
40°-50°	66.7	4.2
50°-60°	16.9	1.1
60°-70°	12.6	0.8
70°-80°	7.5	0.5
80°-90°	2.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1254.8	79.3
0°-40°	1476.2	93.3
0°-60°	1559.8	98.6
0°-90°	1582.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1582.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2709	
5°	2636	244
15°	1991	547
25°	1013	464
35°	340	221
45°	81	67
55°	18	17
65°	13	13
75°	7	7
85°	1	2
90°	0	

TEST NUMBER: P1263492

CATALOG NUMBER: P3AS20R459727D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2709.3
2.5°	2692.3
5°	2635.7
7.5°	2538.1
10°	2395.2
12.5°	2205.6
15°	1990.6
17.5°	1751.5
20°	1502.5
22.5°	1249.2
25°	1013.0
27.5°	797.9
30°	609.8
32.5°	458.4
35°	339.5
37.5°	250.4
40°	179.7
42.5°	124.5
45°	80.6
47.5°	45.3
50°	25.5
52.5°	19.8
55°	18.4
57.5°	17.0
60°	15.6
62.5°	14.1
65°	12.7
67.5°	11.3
70°	9.9
72.5°	8.5
75°	7.1
77.5°	5.7
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)