

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262572

Luminaire Tested: P3AS13R129727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262572
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R129727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 580.0 lumens
Efficiency: N/A
Efficacy: 37.4 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 15.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262572

CATALOG NUMBER: P3AS13R129727DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262572

CATALOG NUMBER: P3AS13R129727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	71	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	48	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146304
5°	142328
10°	130058
15°	113917
20°	97728
25°	81610
30°	65301
35°	48988
40°	35552
45°	23227
50°	14533
55°	9825
60°	8684
65°	7990
70°	7565
75°	6863
80°	6440
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23227 cd/sqm

TEST NUMBER: P1262572

CATALOG NUMBER: P3AS13R129727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.7	10.3
10°-20°	139.8	24.1
20°-30°	154.1	26.6
30°-40°	115.4	19.9
40°-50°	59.8	10.3
50°-60°	24.8	4.3
60°-70°	15.3	2.6
70°-80°	8.6	1.5
80°-90°	2.5	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	353.6	61.0
0°-40°	468.9	80.9
0°-60°	553.5	95.4
0°-90°	580.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	580.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	667	
5°	647	60
15°	502	140
25°	337	154
35°	183	115
45°	75	60
55°	26	25
65°	15	15
75°	8	9
85°	2	2
90°	0	

TEST NUMBER: P1262572

CATALOG NUMBER: P3AS13R129727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	667.2
1°	667.9
2°	665.7
3°	661.3
4°	654.7
5°	646.6
6°	636.3
7°	625.3
8°	612.1
9°	598.1
10°	584.1
12.5°	543.7
15°	501.8
17.5°	460.0
20°	418.8
22.5°	376.9
25°	337.3
27.5°	297.6
30°	257.9
32.5°	219.0
35°	183.0
37.5°	152.1
40°	124.2
42.5°	98.5
45°	74.9
47.5°	56.6
50°	42.6
52.5°	31.6
55°	25.7
57.5°	22.8
60°	19.8
62.5°	17.6
65°	15.4
67.5°	13.2
70°	11.8
72.5°	9.6
75°	8.1
77.5°	6.6
80°	5.1
82.5°	3.7
85°	2.2
87.5°	0.7
90°	0.0

(END OF REPORT)