

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262602

Luminaire Tested: P3AS13R159727DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159727DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 642.0 lumens
Efficiency: N/A
Efficacy: 44.0 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262602
CATALOG NUMBER: P3AS13R159727DE010 E3DLD1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1262602
 CATALOG NUMBER: P3AS13R159727DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91				91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83				83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76				76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70				70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65				65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60				60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56				56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52				52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49				49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161939
5°	157539
10°	143974
15°	126107
20°	108183
25°	90320
30°	72290
35°	54208
40°	39331
45°	25739
50°	16102
55°	10896
60°	9648
65°	8873
70°	8335
75°	7540
80°	7198
85°	6038

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 25739 cd/sqm



TEST NUMBER: P1262602

CATALOG NUMBER: P3AS13R159727DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.0	10.3
10°-20°	154.8	24.1
20°-30°	170.5	26.6
30°-40°	127.7	19.9
40°-50°	66.2	10.3
50°-60°	27.5	4.3
60°-70°	17.0	2.6
70°-80°	9.5	1.5
80°-90°	2.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	391.4	61.0
0°-40°	519.1	80.9
0°-60°	612.7	95.4
0°-90°	642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	642.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	738	
5°	716	66
15°	556	155
25°	373	171
35°	202	128
45°	83	66
55°	28	27
65°	17	17
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1262602
CATALOG NUMBER: P3AS13R159727DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	738.5
1°	739.3
2°	736.9
3°	732.0
4°	724.7
5°	715.7
6°	704.3
7°	692.1
8°	677.5
9°	662.0
10°	646.6
12.5°	601.9
15°	555.5
17.5°	509.1
20°	463.6
22.5°	417.2
25°	373.3
27.5°	329.4
30°	285.5
32.5°	242.4
35°	202.5
37.5°	168.4
40°	137.4
42.5°	109.0
45°	83.0
47.5°	62.6
50°	47.2
52.5°	35.0
55°	28.5
57.5°	25.2
60°	22.0
62.5°	19.5
65°	17.1
67.5°	14.6
70°	13.0
72.5°	10.6
75°	8.9
77.5°	7.3
80°	5.7
82.5°	4.1
85°	2.4
87.5°	0.8
90°	0.0

(END OF REPORT)