

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263518

Luminaire Tested: P3AS20R509727D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263518
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509727D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 780.0 lumens
Efficiency: N/A
Efficacy: 27.1 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263518

CATALOG NUMBER: P3AS20R509727D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263518

CATALOG NUMBER: P3AS20R509727D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	248335
5°	243341
10°	227918
15°	204042
20°	171702
25°	131040
30°	85178
35°	50487
40°	29169
45°	14637
50°	5458
55°	4244
60°	3947
65°	3580
70°	3526
75°	3558
80°	3536
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 14637 cd/sqm

TEST NUMBER: P1263518

CATALOG NUMBER: P3AS20R509727D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	13.2
10°-20°	248.6	31.9
20°-30°	243.8	31.3
30°-40°	122.8	15.7
40°-50°	38.8	5.0
50°-60°	10.1	1.3
60°-70°	7.1	0.9
70°-80°	4.4	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	595.2	76.3
0°-40°	718.1	92.1
0°-60°	767.0	98.3
0°-90°	780.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	780.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1132	
5°	1106	103
15°	899	249
25°	542	244
35°	189	123
45°	47	39
55°	11	10
65°	7	7
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1263518

CATALOG NUMBER: P3AS20R509727D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1132.5
2.5°	1125.6
5°	1105.5
7.5°	1069.4
10°	1023.6
12.5°	964.7
15°	898.8
17.5°	822.5
20°	735.8
22.5°	642.2
25°	541.6
27.5°	434.8
30°	336.4
32.5°	253.1
35°	188.6
37.5°	139.4
40°	101.9
42.5°	72.1
45°	47.2
47.5°	27.0
50°	16.0
52.5°	11.8
55°	11.1
57.5°	9.7
60°	9.0
62.5°	8.3
65°	6.9
67.5°	6.2
70°	5.5
72.5°	4.9
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)