

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263523

Luminaire Tested: P3AS20R509727D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509727D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1592.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263523

CATALOG NUMBER: P3AS20R509727D010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263523

CATALOG NUMBER: P3AS20R509727D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82		
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67		
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64		
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60		
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57		
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	506867
5°	496653
10°	465211
15°	416461
20°	350450
25°	267475
30°	173824
35°	103062
40°	59569
45°	29864
50°	11121
55°	8640
60°	8070
65°	7368
70°	7245
75°	7202
80°	7198
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29864 cd/sqm

TEST NUMBER: P1263523

CATALOG NUMBER: P3AS20R509727D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	209.9	13.2
10°-20°	507.3	31.9
20°-30°	497.7	31.3
30°-40°	250.7	15.8
40°-50°	79.2	5.0
50°-60°	20.5	1.3
60°-70°	14.5	0.9
70°-80°	9.0	0.6
80°-90°	3.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1214.9	76.3
0°-40°	1465.7	92.1
0°-60°	1565.4	98.3
0°-90°	1592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1592.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2312	
5°	2256	210
15°	1834	507
25°	1106	498
35°	385	251
45°	96	79
55°	23	21
65°	14	15
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1263523

CATALOG NUMBER: P3AS20R509727D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2311.5
2.5°	2297.3
5°	2256.3
7.5°	2182.7
10°	2089.3
12.5°	1968.9
15°	1834.5
17.5°	1678.8
20°	1501.8
22.5°	1310.7
25°	1105.5
27.5°	887.5
30°	686.5
32.5°	516.7
35°	385.0
37.5°	284.5
40°	208.1
42.5°	147.2
45°	96.3
47.5°	55.2
50°	32.6
52.5°	24.1
55°	22.6
57.5°	19.8
60°	18.4
62.5°	17.0
65°	14.2
67.5°	12.7
70°	11.3
72.5°	9.9
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)