

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262608

Luminaire Tested: P3AS13R159727DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262608
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R159727DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 501.0 lumens
Efficiency: N/A
Efficacy: 34.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262608

CATALOG NUMBER: P3AS13R159727DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262608

CATALOG NUMBER: P3AS13R159727DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216035
5°	199669
10°	159405
15°	120409
20°	91708
25°	69875
30°	50058
35°	32658
40°	20038
45°	12125
50°	8051
55°	6232
60°	5350
65°	4618
70°	4167
75°	4151
80°	3031
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 12125 cd/sqm

TEST NUMBER: P1262608

CATALOG NUMBER: P3AS13R159727DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	16.0
10°-20°	148.3	29.6
20°-30°	132.0	26.3
30°-40°	78.1	15.6
40°-50°	32.1	6.4
50°-60°	15.0	3.0
60°-70°	9.1	1.8
70°-80°	4.8	1.0
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.6	72.0
0°-40°	438.7	87.6
0°-60°	485.8	97.0
0°-90°	501.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	985	
5°	907	80
15°	530	148
25°	289	132
35°	122	78
45°	39	32
55°	16	15
65°	9	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1262608

CATALOG NUMBER: P3AS13R159727DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	985.2
1°	982.8
2°	975.5
3°	960.8
4°	936.4
5°	907.1
6°	875.4
7°	838.0
8°	798.9
9°	759.1
10°	715.9
12.5°	617.5
15°	530.4
17.5°	455.6
20°	393.0
22.5°	337.6
25°	288.8
27.5°	241.6
30°	197.7
32.5°	157.8
35°	122.0
37.5°	93.6
40°	70.0
42.5°	52.1
45°	39.1
47.5°	30.1
50°	23.6
52.5°	19.5
55°	16.3
57.5°	13.8
60°	12.2
62.5°	10.6
65°	8.9
67.5°	8.1
70°	6.5
72.5°	5.7
75°	4.9
77.5°	3.3
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)