

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263611

Luminaire Tested: P3AS20R659727D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1263611  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R659727D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R65 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 546.0 lumens  
Efficiency: N/A  
Efficacy: 19.0 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263611

CATALOG NUMBER: P3AS20R659727D010 E3DLD1GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1263611

CATALOG NUMBER: P3AS20R659727D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 101 | 102 | 100 | 98  |  | 99  | 97  | 95  |  | 95  |
| 2   | 105 | 99  | 94  | 90  | 103 | 97  | 93  | 89  | 94  | 90  | 87  |  | 91  | 88  | 85  |  | 88  |
| 3   | 99  | 91  | 85  | 80  | 96  | 89  | 84  | 79  | 87  | 82  | 78  |  | 84  | 80  | 77  |  | 82  |
| 4   | 92  | 83  | 77  | 72  | 90  | 82  | 76  | 71  | 80  | 75  | 70  |  | 78  | 73  | 70  |  | 76  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 69  | 65  | 74  | 68  | 64  |  | 72  | 67  | 63  |  | 71  |
| 6   | 82  | 71  | 64  | 59  | 80  | 70  | 64  | 59  | 69  | 63  | 58  |  | 67  | 62  | 58  |  | 66  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  |  | 63  | 57  | 53  |  | 61  |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  |  | 59  | 53  | 49  |  | 58  |
| 9   | 68  | 57  | 51  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  |  | 55  | 49  | 46  |  | 54  |
| 10  | 65  | 54  | 47  | 43  | 64  | 53  | 47  | 43  | 52  | 47  | 43  |  | 52  | 46  | 42  |  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 97163 |
| 5°  | 95862 |
| 10° | 92650 |
| 15° | 87378 |
| 20° | 80577 |
| 25° | 73141 |
| 30° | 64795 |
| 35° | 55118 |
| 40° | 43854 |
| 45° | 30980 |
| 50° | 17978 |
| 55° | 9825  |
| 60° | 9122  |
| 65° | 8250  |
| 70° | 7565  |
| 75° | 7032  |
| 80° | 6188  |
| 85° | 5284  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30980 cd/sqm

TEST NUMBER: P1263611

CATALOG NUMBER: P3AS20R659727D010 E3DLD1GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 41.0   | 7.5       |
| 10°-20°   | 107.7  | 19.7      |
| 20°-30°   | 138.4  | 25.3      |
| 30°-40°   | 128.0  | 23.4      |
| 40°-50°   | 77.3   | 14.2      |
| 50°-60°   | 26.4   | 4.8       |
| 60°-70°   | 15.9   | 2.9       |
| 70°-80°   | 9.0    | 1.6       |
| 80°-90°   | 2.6    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 287.0  | 52.6      |
| 0°-40°    | 415.0  | 76.0      |
| 0°-60°    | 518.7  | 95.0      |
| 0°-90°    | 546.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 546.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 443 |      |
| 5°  | 436 | 41   |
| 15° | 385 | 108  |
| 25° | 302 | 138  |
| 35° | 206 | 128  |
| 45° | 100 | 77   |
| 55° | 26  | 26   |
| 65° | 16  | 16   |
| 75° | 8   | 9    |
| 85° | 2   | 3    |
| 90° | 0   |      |

TEST NUMBER: P1263611

CATALOG NUMBER: P3AS20R659727D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 443.1 |
| 2.5°  | 441.0 |
| 5°    | 435.5 |
| 7.5°  | 427.2 |
| 10°   | 416.1 |
| 12.5° | 402.2 |
| 15°   | 384.9 |
| 17.5° | 366.1 |
| 20°   | 345.3 |
| 22.5° | 323.8 |
| 25°   | 302.3 |
| 27.5° | 279.5 |
| 30°   | 255.9 |
| 32.5° | 232.3 |
| 35°   | 205.9 |
| 37.5° | 180.3 |
| 40°   | 153.2 |
| 42.5° | 126.2 |
| 45°   | 99.9  |
| 47.5° | 75.6  |
| 50°   | 52.7  |
| 52.5° | 33.3  |
| 55°   | 25.7  |
| 57.5° | 22.9  |
| 60°   | 20.8  |
| 62.5° | 18.0  |
| 65°   | 15.9  |
| 67.5° | 13.9  |
| 70°   | 11.8  |
| 72.5° | 10.4  |
| 75°   | 8.3   |
| 77.5° | 6.9   |
| 80°   | 4.9   |
| 82.5° | 3.5   |
| 85°   | 2.1   |
| 87.5° | 1.4   |
| 90°   | 0.0   |

(END OF REPORT)