

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263629

Luminaire Tested: P3AS20R709727D010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263629  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R709727D010 E3D1H  
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1688.0 lumens  
Efficiency: N/A  
Efficacy: 58.6 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263629  
CATALOG NUMBER: P3AS20R709727D010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1263629  
 CATALOG NUMBER: P3AS20R709727D010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79			
4	95	87	81	77	94	86	81	77	84	79	76	82	78	75	80	77	74	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	328219
5°	309486
10°	293448
15°	288174
20°	277784
25°	261838
30°	259989
35°	226414
40°	146446
45°	69216
50°	9688
55°	803
60°	614
65°	726
70°	449
75°	593
80°	884
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 69216 cd/sqm



TEST NUMBER: P1263629  
 CATALOG NUMBER: P3AS20R709727D010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	131.3	7.8
10°-20°	356.5	21.1
20°-30°	504.3	29.9
30°-40°	506.8	30.0
40°-50°	182.2	10.8
50°-60°	4.9	0.3
60°-70°	1.1	0.1
70°-80°	0.7	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	992.1	58.8
0°-40°	1498.9	88.8
0°-60°	1686.0	99.9
0°-90°	1688.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1688.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1497	
5°	1406	131
15°	1269	356
25°	1082	504
35°	846	507
45°	223	182
55°	2	5
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1263629  
CATALOG NUMBER: P3AS20R709727D010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1496.8
1°	1492.6
2°	1479.5
3°	1458.7
4°	1432.3
5°	1406.0
6°	1381.0
7°	1361.6
8°	1344.3
9°	1330.4
10°	1317.9
11°	1307.5
12°	1297.8
13°	1288.1
14°	1279.1
15°	1269.4
16°	1257.6
17°	1245.1
18°	1229.9
19°	1211.2
20°	1190.4
21°	1167.5
22°	1144.6
23°	1122.4
24°	1100.9
25°	1082.2
26°	1069.0
27°	1058.6
28°	1050.3
29°	1040.6
30°	1026.8
31°	1006.7
32°	978.2
32.5°	962.3
33°	940.8
34°	898.5
35°	845.8
36°	787.6
37°	721.7
37.5°	691.2
38°	649.6
39°	575.4
40°	511.6
42.5°	354.3
45°	223.2



TEST NUMBER: P1263629  
CATALOG NUMBER: P3AS20R709727D010 E3D1H

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	119.9
50°	28.4
52.5°	3.5
55°	2.1
57.5°	2.1
60°	1.4
62.5°	1.4
65°	1.4
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)