

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263755

Luminaire Tested: P3AS02R129730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263755
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 133.0 lumens
Efficiency: N/A
Efficacy: 35.9 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263755

CATALOG NUMBER: P3AS02R129730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263755

CATALOG NUMBER: P3AS02R129730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		93
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		86
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		80
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		75
5	93	84	78	74	91	83	78	74	81	77	73		80	76	73		70
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		66
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		62
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		56
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57342
5°	53004
10°	42328
15°	31964
20°	24339
25°	18558
30°	13293
35°	8673
40°	5324
45°	3225
50°	2149
55°	1644
60°	1403
65°	1245
70°	1090
75°	1101
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3225 cd/sqm

TEST NUMBER: P1263755

CATALOG NUMBER: P3AS02R129730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.3	16.0
10°-20°	39.4	29.6
20°-30°	35.0	26.3
30°-40°	20.7	15.6
40°-50°	8.5	6.4
50°-60°	4.0	3.0
60°-70°	2.4	1.8
70°-80°	1.3	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.7	72.0
0°-40°	116.5	87.6
0°-60°	129.0	97.0
0°-90°	133.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	133.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	262	
5°	241	21
15°	141	39
25°	77	35
35°	32	21
45°	10	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263755

CATALOG NUMBER: P3AS02R129730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	261.5
1°	260.9
2°	259.0
3°	255.1
4°	248.6
5°	240.8
6°	232.4
7°	222.5
8°	212.1
9°	201.5
10°	190.1
12.5°	163.9
15°	140.8
17.5°	120.9
20°	104.3
22.5°	89.6
25°	76.7
27.5°	64.1
30°	52.5
32.5°	41.9
35°	32.4
37.5°	24.8
40°	18.6
42.5°	13.8
45°	10.4
47.5°	8.0
50°	6.3
52.5°	5.2
55°	4.3
57.5°	3.7
60°	3.2
62.5°	2.8
65°	2.4
67.5°	2.2
70°	1.7
72.5°	1.5
75°	1.3
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)