

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263757

Luminaire Tested: P3AS02R129730DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R129730DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R12 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 166.0 lumens
Efficiency: N/A
Efficacy: 44.9 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263757

CATALOG NUMBER: P3AS02R129730DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1263757

CATALOG NUMBER: P3AS02R129730DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	47	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48308
5°	45278
10°	37140
15°	28854
20°	22775
25°	18146
30°	14559
35°	11886
40°	9790
45°	8249
50°	7096
55°	6117
60°	5438
65°	4722
70°	4231
75°	3389
80°	2778
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8249 cd/sqm

TEST NUMBER: P1263757

CATALOG NUMBER: P3AS02R129730DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.4	11.1
10°-20°	35.6	21.4
20°-30°	34.6	20.8
30°-40°	28.0	16.8
40°-50°	20.8	12.5
50°-60°	14.5	8.7
60°-70°	9.1	5.5
70°-80°	4.3	2.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.6	53.4
0°-40°	116.5	70.2
0°-60°	151.8	91.4
0°-90°	166.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	166.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	220	
5°	206	18
15°	127	36
25°	75	35
35°	44	28
45°	27	21
55°	16	15
65°	9	9
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1263757

CATALOG NUMBER: P3AS02R129730DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	220.3
2.5°	216.7
5°	205.7
7.5°	188.3
10°	166.8
12.5°	145.7
15°	127.1
17.5°	111.4
20°	97.6
22.5°	85.6
25°	75.0
27.5°	65.5
30°	57.5
32.5°	50.6
35°	44.4
37.5°	39.0
40°	34.2
42.5°	30.2
45°	26.6
47.5°	23.7
50°	20.8
52.5°	18.2
55°	16.0
57.5°	14.2
60°	12.4
62.5°	10.6
65°	9.1
67.5°	7.6
70°	6.6
72.5°	5.1
75°	4.0
77.5°	2.9
80°	2.2
82.5°	1.1
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)