

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262677

Luminaire Tested: P3AS13R309727DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262677
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309727DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1027.0 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262677

CATALOG NUMBER: P3AS13R309727DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1262677

CATALOG NUMBER: P3AS13R309727DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	90	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	88	87	86
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	99	92	88	85	97	92	88	85	90	87	85	89	86	84	88	85	83	82	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	80	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	76	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	817106
5°	806447
10°	704106
15°	447539
20°	177325
25°	59229
30°	27549
35°	12474
40°	4780
45°	2357
50°	682
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2357 cd/sqm

TEST NUMBER: P1262677

CATALOG NUMBER: P3AS13R309727DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	335.0	32.6
10°-20°	519.4	50.6
20°-30°	133.9	13.0
30°-40°	31.5	3.1
40°-50°	6.2	0.6
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	988.4	96.2
0°-40°	1019.8	99.3
0°-60°	1026.7	100.0
0°-90°	1027.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1027.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3726	
5°	3664	335
15°	1971	519
25°	245	134
35°	47	31
45°	8	6
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1262677

CATALOG NUMBER: P3AS13R309727DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3726.3
1°	3723.5
2°	3714.8
3°	3704.8
4°	3690.1
5°	3663.7
6°	3621.1
7°	3550.1
8°	3453.2
9°	3326.9
10°	3162.2
11°	2966.5
12°	2752.8
13°	2506.8
14°	2249.3
15°	1971.4
16°	1699.1
17°	1436.8
18°	1185.2
19°	954.4
20°	759.9
21°	598.0
22°	470.4
23°	372.4
24°	298.2
25°	244.8
26°	204.1
27°	173.4
28°	149.9
29°	128.4
30°	108.8
32.5°	68.6
35°	46.6
37.5°	29.1
40°	16.7
42.5°	11.2
45°	7.6
47.5°	4.4
50°	2.0
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4



TEST NUMBER: P1262677

CATALOG NUMBER: P3AS13R309727DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)