

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263776

Luminaire Tested: P3AS02R159730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 84.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263776

CATALOG NUMBER: P3AS02R159730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263776

CATALOG NUMBER: P3AS02R159730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	95	91	95	92	89		92	90	87		90
3	100	93	87	83	98	91	86	82	89	84	81		86	82	79		84
4	94	86	80	75	92	85	79	74	82	77	73		80	76	73		78
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		74
6	84	74	68	63	83	73	67	63	72	66	62		70	66	62		69
7	80	69	63	58	78	69	63	58	67	62	58		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	61	55	51	71	61	55	51	60	54	50		59	54	50		58
10	68	58	52	47	67	57	51	47	57	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21183
5°	20603
10°	18837
15°	16504
20°	14165
25°	11807
30°	9470
35°	7094
40°	5153
45°	3380
50°	2115
55°	1415
60°	1272
65°	1141
70°	1090
75°	1017
80°	884
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3380 cd/sqm

TEST NUMBER: P1263776

CATALOG NUMBER: P3AS02R159730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.6	10.3
10°-20°	20.3	24.1
20°-30°	22.3	26.6
30°-40°	16.7	19.9
40°-50°	8.7	10.3
50°-60°	3.6	4.3
60°-70°	2.2	2.6
70°-80°	1.3	1.5
80°-90°	0.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	51.2	60.9
0°-40°	67.9	80.8
0°-60°	80.2	95.4
0°-90°	84.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	84.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	97	
5°	94	9
15°	73	20
25°	49	22
35°	26	17
45°	11	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263776

CATALOG NUMBER: P3AS02R159730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	96.6
1°	96.7
2°	96.4
3°	95.8
4°	94.8
5°	93.6
6°	92.2
7°	90.6
8°	88.6
9°	86.6
10°	84.6
12.5°	78.7
15°	72.7
17.5°	66.6
20°	60.7
22.5°	54.6
25°	48.8
27.5°	43.1
30°	37.4
32.5°	31.7
35°	26.5
37.5°	22.0
40°	18.0
42.5°	14.3
45°	10.9
47.5°	8.2
50°	6.2
52.5°	4.6
55°	3.7
57.5°	3.3
60°	2.9
62.5°	2.6
65°	2.2
67.5°	1.9
70°	1.7
72.5°	1.4
75°	1.2
77.5°	1.0
80°	0.7
82.5°	0.5
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)