

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262683

Luminaire Tested: P3AS13R309727DE010 E3DL1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1262683  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R309727DE010 E3DL1LI  
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 861.9 lumens  
Efficiency: N/A  
Efficacy: 59.0 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1262683  
CATALOG NUMBER: P3AS13R309727DE010 E3DL1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1262683  
 CATALOG NUMBER: P3AS13R309727DE010 E3DL1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	503008
5°	478757
10°	402709
15°	290422
20°	180149
25°	102441
30°	56895
35°	30945
40°	16316
45°	8838
50°	4708
55°	3097
60°	2851
65°	2958
70°	2629
75°	2033
80°	2020
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8838 cd/sqm



TEST NUMBER: P1262683  
 CATALOG NUMBER: P3AS13R309727DE010 E3DL1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.8	22.7
10°-20°	348.1	40.4
20°-30°	201.2	23.3
30°-40°	76.3	8.9
40°-50°	23.4	2.7
50°-60°	7.9	0.9
60°-70°	5.3	0.6
70°-80°	2.9	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	745.2	86.5
0°-40°	821.5	95.3
0°-60°	852.8	98.9
0°-90°	861.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	861.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2294	
5°	2175	196
15°	1279	348
25°	423	201
35°	116	76
45°	28	23
55°	8	8
65°	6	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1262683  
CATALOG NUMBER: P3AS13R309727DE010 E3DL1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2293.9
1°	2292.3
2°	2278.4
3°	2252.4
4°	2219.8
5°	2175.0
6°	2118.0
7°	2054.5
8°	1983.6
9°	1898.9
10°	1808.6
11°	1710.8
12°	1607.4
13°	1499.1
14°	1389.2
15°	1279.3
17.5°	1008.9
20°	772.0
22.5°	572.5
25°	423.4
27.5°	307.8
30°	224.7
32.5°	162.0
35°	115.6
37.5°	80.6
40°	57.0
42.5°	39.9
45°	28.5
47.5°	19.5
50°	13.8
52.5°	9.8
55°	8.1
57.5°	7.3
60°	6.5
62.5°	5.7
65°	5.7
67.5°	4.9
70°	4.1
72.5°	3.3
75°	2.4
77.5°	2.4
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.0



TEST NUMBER: P1262683  
CATALOG NUMBER: P3AS13R309727DE010 E3DL1LI

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)