

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263784

Luminaire Tested: P3AS02R159730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 135.0 lumens
Efficiency: N/A
Efficacy: 37.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263784
CATALOG NUMBER: P3AS02R159730DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1263784
 CATALOG NUMBER: P3AS02R159730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	98
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	92	91
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	85	84
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	79	78
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	74	73
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	69	68
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	65	64
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	61	60
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	58	57
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	55	54
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	52	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	58219
5°	53797
10°	42952
15°	32441
20°	24712
25°	18824
30°	13496
35°	8807
40°	5410
45°	3256
50°	2183
55°	1682
60°	1447
65°	1245
70°	1154
75°	1101
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3256 cd/sqm



TEST NUMBER: P1263784
 CATALOG NUMBER: P3AS02R159730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.7	16.0
10°-20°	40.0	29.6
20°-30°	35.6	26.3
30°-40°	21.0	15.6
40°-50°	8.6	6.4
50°-60°	4.1	3.0
60°-70°	2.5	1.8
70°-80°	1.3	1.0
80°-90°	0.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	97.2	72.0
0°-40°	118.2	87.6
0°-60°	130.9	97.0
0°-90°	135.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	135.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	266	
5°	244	22
15°	143	40
25°	78	36
35°	33	21
45°	10	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1263784
CATALOG NUMBER: P3AS02R159730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	265.5
1°	264.8
2°	262.9
3°	258.9
4°	252.3
5°	244.4
6°	235.9
7°	225.8
8°	215.3
9°	204.5
10°	192.9
12.5°	166.4
15°	142.9
17.5°	122.8
20°	105.9
22.5°	91.0
25°	77.8
27.5°	65.1
30°	53.3
32.5°	42.5
35°	32.9
37.5°	25.2
40°	18.9
42.5°	14.0
45°	10.5
47.5°	8.1
50°	6.4
52.5°	5.3
55°	4.4
57.5°	3.7
60°	3.3
62.5°	2.8
65°	2.4
67.5°	2.2
70°	1.8
72.5°	1.5
75°	1.3
77.5°	0.9
80°	0.7
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)