

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263788

Luminaire Tested: P3AS02R159730DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R159730DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 187.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.31 / 0.31 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263788
CATALOG NUMBER: P3AS02R159730DE010 E3PH1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1263788

CATALOG NUMBER: P3AS02R159730DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	113	111	114	112	111	110	108	107	106	105	104	103	101	101	100	99	99	99	99
2	113	110	108	106	111	109	107	105	106	104	103	103	102	100	100	99	98	98	98	98	97
3	111	107	104	102	109	106	103	101	104	101	100	101	100	98	99	98	97	97	97	97	96
4	109	104	101	99	107	103	101	99	102	99	98	100	98	97	98	97	95	95	95	95	94
5	107	102	99	97	105	101	99	96	100	98	96	99	96	95	97	96	94	94	94	94	93
6	105	100	97	95	104	100	97	95	98	96	94	97	95	93	96	94	93	93	93	93	92
7	103	98	95	93	102	98	95	93	97	94	93	96	94	92	95	93	92	92	92	92	91
8	101	97	94	92	101	96	94	92	96	93	91	95	93	91	94	92	91	91	91	91	90
9	100	95	92	90	99	95	92	90	94	92	90	94	91	90	93	91	90	90	90	90	89
10	99	94	91	89	98	94	91	89	93	91	89	93	90	89	92	90	89	89	89	89	88

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	394289
5°	341844
10°	166218
15°	35460
20°	7444
25°	2226
30°	481
35°	80
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 0 cd/sqm



TEST NUMBER: P1263788
 CATALOG NUMBER: P3AS02R159730DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	64.9
10°-20°	60.3	32.3
20°-30°	5.0	2.7
30°-40°	0.3	0.2
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.7	99.8
0°-40°	187.0	100.0
0°-60°	187.0	100.0
0°-90°	187.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	187.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1798	
5°	1553	121
15°	156	60
25°	9	5
35°	0	0
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263788
CATALOG NUMBER: P3AS02R159730DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1798.1
2.5°	1735.1
5°	1553.0
7.5°	1189.1
10°	746.5
12.5°	359.2
15°	156.2
17.5°	79.7
20°	31.9
22.5°	15.8
25°	9.2
27.5°	4.7
30°	1.9
32.5°	0.6
35°	0.3
37.5°	0.3
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)