

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263800

Luminaire Tested: P3AS02R209730DE010 E3D1WH

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263800  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R209730DE010 E3D1WH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 274.0 lumens  
Efficiency: N/A  
Efficacy: 76.1 lumens/watt  
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263800  
CATALOG NUMBER: P3AS02R209730DE010 E3D1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1263800  
 CATALOG NUMBER: P3AS02R209730DE010 E3D1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	95	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	93	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	91	91	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	89	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	87	87	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	85	85	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	83	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	81	81	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	80	80	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	415647
5°	349944
10°	218566
15°	81726
20°	28049
25°	11686
30°	5495
35°	2463
40°	1174
45°	589
50°	205
55°	38
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 589 cd/sqm



TEST NUMBER: P1263800  
 CATALOG NUMBER: P3AS02R209730DE010 E3D1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	132.2	48.3
10°-20°	108.9	39.7
20°-30°	24.7	9.0
30°-40°	6.3	2.3
40°-50°	1.6	0.6
50°-60°	0.2	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	265.8	97.0
0°-40°	272.1	99.3
0°-60°	273.9	100.0
0°-90°	274.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	274.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1896	
5°	1590	132
15°	360	109
25°	48	25
35°	9	6
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1263800  
CATALOG NUMBER: P3AS02R209730DE010 E3D1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1895.5
1°	1879.4
2°	1832.0
3°	1764.1
4°	1680.8
5°	1589.8
6°	1488.5
7°	1376.6
8°	1246.1
9°	1116.8
10°	981.6
11°	837.8
12°	694.1
13°	572.4
14°	456.1
15°	360.0
16°	284.1
17°	224.1
18°	180.1
19°	146.4
20°	120.2
21°	100.5
22°	83.9
23°	69.7
24°	58.2
25°	48.3
27.5°	31.6
30°	21.7
32.5°	13.4
35°	9.2
37.5°	5.9
40°	4.1
42.5°	2.8
45°	1.9
47.5°	1.3
50°	0.6
52.5°	0.3
55°	0.1
57.5°	0.1
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1263800  
CATALOG NUMBER: P3AS02R209730DE010 E3D1WH

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)