

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262792

Luminaire Tested: P3AS13R509727DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509727DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1113.9 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262792
CATALOG NUMBER: P3AS13R509727DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1262792
 CATALOG NUMBER: P3AS13R509727DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65	65	65	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59	59	59	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	387973
5°	381025
10°	365858
15°	335484
20°	295822
25°	226755
30°	123285
35°	39672
40°	9332
45°	1271
50°	1126
55°	1262
60°	1053
65°	1245
70°	1026
75°	1356
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 2013 cd/sqm



TEST NUMBER: P1262792
 CATALOG NUMBER: P3AS13R509727DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.4	14.6
10°-20°	410.8	36.9
20°-30°	411.4	36.9
30°-40°	115.7	10.4
40°-50°	7.0	0.6
50°-60°	2.6	0.2
60°-70°	2.1	0.2
70°-80°	1.4	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	984.6	88.4
0°-40°	1100.3	98.8
0°-60°	1110.0	99.6
0°-90°	1113.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1113.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1769	
5°	1731	162
15°	1478	411
25°	937	411
35°	148	116
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P1262792
CATALOG NUMBER: P3AS13R509727DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1769.3
2.5°	1760.3
5°	1731.0
7.5°	1691.1
10°	1643.1
12.5°	1570.6
15°	1477.8
17.5°	1371.1
20°	1267.7
22.5°	1139.1
25°	937.2
27.5°	697.8
30°	486.9
32.5°	293.9
35°	148.2
37.5°	70.0
40°	32.6
42.5°	12.2
45°	4.1
47.5°	3.3
50°	3.3
52.5°	3.3
55°	3.3
57.5°	2.4
60°	2.4
62.5°	2.4
65°	2.4
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)