

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262811

Luminaire Tested: P3AS13R509727DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262811
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R509727DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 915.0 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262811

CATALOG NUMBER: P3AS13R509727DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1262811

CATALOG NUMBER: P3AS13R509727DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	91	85	81	96	90	85	81	87	83	80		85	82	79		84
5	93	85	80	75	92	84	79	75	83	78	74		81	77	74		79
6	89	80	75	71	88	80	74	70	78	73	70		77	73	69		75
7	85	76	70	66	84	75	70	66	74	69	66		73	69	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	62		68
9	78	68	63	59	76	68	62	59	67	62	59		66	62	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	291314
5°	285449
10°	267374
15°	239366
20°	201431
25°	153735
30°	99914
35°	59240
40°	34236
45°	17149
50°	6379
55°	4970
60°	4649
65°	4203
70°	4167
75°	4151
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17149 cd/sqm

TEST NUMBER: P1262811

CATALOG NUMBER: P3AS13R509727DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.6	13.2
10°-20°	291.6	31.9
20°-30°	286.1	31.3
30°-40°	144.1	15.7
40°-50°	45.5	5.0
50°-60°	11.8	1.3
60°-70°	8.3	0.9
70°-80°	5.2	0.6
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.3	76.3
0°-40°	842.4	92.1
0°-60°	899.7	98.3
0°-90°	915.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	915.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1328	
5°	1297	121
15°	1054	292
25°	635	286
35°	221	144
45°	55	46
55°	13	12
65°	8	8
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1262811

CATALOG NUMBER: P3AS13R509727DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1328.5
2.5°	1320.4
5°	1296.8
7.5°	1254.5
10°	1200.8
12.5°	1131.6
15°	1054.4
17.5°	964.9
20°	863.2
22.5°	753.3
25°	635.4
27.5°	510.1
30°	394.6
32.5°	296.9
35°	221.3
37.5°	163.5
40°	119.6
42.5°	84.6
45°	55.3
47.5°	31.7
50°	18.7
52.5°	13.8
55°	13.0
57.5°	11.4
60°	10.6
62.5°	9.8
65°	8.1
67.5°	7.3
70°	6.5
72.5°	5.7
75°	4.9
77.5°	4.1
80°	3.3
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)