

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263809

Luminaire Tested: P3AS02R209730DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263809
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209730DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 172.0 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263809
CATALOG NUMBER: P3AS02R209730DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1263809
 CATALOG NUMBER: P3AS02R209730DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42540
5°	41404
10°	38098
15°	33530
20°	28749
25°	24147
30°	19522
35°	14857
40°	10563
45°	6977
50°	4332
55°	2829
60°	2588
65°	2387
70°	2244
75°	2033
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6977 cd/sqm



TEST NUMBER: P1263809
 CATALOG NUMBER: P3AS02R209730DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.4	10.1
10°-20°	41.1	23.9
20°-30°	45.6	26.5
30°-40°	34.8	20.2
40°-50°	17.8	10.4
50°-60°	7.3	4.3
60°-70°	4.6	2.6
70°-80°	2.6	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.2	60.6
0°-40°	139.0	80.8
0°-60°	164.1	95.4
0°-90°	172.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	172.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	194	
5°	188	17
15°	148	41
25°	100	46
35°	56	35
45°	22	18
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1263809
CATALOG NUMBER: P3AS02R209730DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	194.0
1°	194.2
2°	193.4
3°	192.3
4°	190.5
5°	188.1
6°	185.3
7°	182.2
8°	178.9
9°	175.0
10°	171.1
12.5°	159.7
15°	147.7
17.5°	135.5
20°	123.2
22.5°	111.0
25°	99.8
27.5°	88.7
30°	77.1
32.5°	66.2
35°	55.5
37.5°	46.1
40°	36.9
42.5°	29.1
45°	22.5
47.5°	17.0
50°	12.7
52.5°	9.4
55°	7.4
57.5°	6.8
60°	5.9
62.5°	5.2
65°	4.6
67.5°	3.9
70°	3.5
72.5°	2.8
75°	2.4
77.5°	2.0
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.2
90°	0.0

(END OF REPORT)