

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1262823

Luminaire Tested: P3AS13R559727DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1262823
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559727DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 2700K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1050.0 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1262823

CATALOG NUMBER: P3AS13R559727DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1262823

CATALOG NUMBER: P3AS13R559727DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	98	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	84	82		86
5	95	88	82	79	94	87	82	78	85	81	78		84	80	77		82
6	91	83	78	74	90	82	77	74	81	76	73		80	76	73		78
7	87	79	73	70	86	78	73	69	77	72	69		76	72	69		75
8	83	75	69	66	82	74	69	66	73	69	65		72	68	65		71
9	80	71	66	62	79	71	66	62	70	65	62		69	65	62		68
10	77	68	62	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	304493
5°	293704
10°	304203
15°	299934
20°	277574
25°	224481
30°	134527
35°	45588
40°	12566
45°	5582
50°	1637
55°	306
60°	175
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5582 cd/sqm

TEST NUMBER: P1262823

CATALOG NUMBER: P3AS13R559727DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	12.3
10°-20°	367.8	35.0
20°-30°	408.9	38.9
30°-40°	127.3	12.1
40°-50°	15.3	1.5
50°-60°	1.2	0.1
60°-70°	0.4	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	905.8	86.3
0°-40°	1033.1	98.4
0°-60°	1049.6	100.0
0°-90°	1050.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1050.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1389	
5°	1334	129
15°	1321	368
25°	928	409
35°	170	127
45°	18	15
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1262823

CATALOG NUMBER: P3AS13R559727DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1388.6
1°	1383.4
2°	1369.8
3°	1353.1
4°	1337.9
5°	1334.3
6°	1338.3
7°	1346.7
8°	1356.3
9°	1363.8
10°	1366.2
11°	1364.6
12°	1358.3
13°	1348.3
14°	1336.7
15°	1321.2
16°	1303.2
17°	1280.5
18°	1254.9
19°	1224.2
20°	1189.5
21°	1150.0
22°	1103.4
23°	1051.9
24°	992.9
25°	927.8
26°	856.4
27°	780.7
28°	699.7
29°	616.3
30°	531.3
31°	446.0
32°	362.6
32.5°	325.5
33°	287.2
34°	222.2
35°	170.3
36°	129.6
37°	96.1
37.5°	82.2
38°	71.4
39°	54.3
40°	43.9
42.5°	27.9
45°	18.0

TEST NUMBER: P1262823

CATALOG NUMBER: P3AS13R559727DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	10.8
50°	4.8
52.5°	1.6
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)