

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263828

Luminaire Tested: P3AS02R259730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263828
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 112.0 lumens
Efficiency: N/A
Efficacy: 31.1 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263828

CATALOG NUMBER: P3AS02R259730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263828

CATALOG NUMBER: P3AS02R259730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	97	97	95
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	92	92	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	87	87	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	83	83	82
5	97	90	85	82	96	89	85	82	88	84	81	86	83	80	85	82	79	79	79	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	76	76	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	73	73	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	70	70	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	67	67	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	65	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71836
5°	67026
10°	53684
15°	36459
20°	22052
25°	12896
30°	7343
35°	4042
40°	2147
45°	1116
50°	648
55°	497
60°	439
65°	467
70°	385
75°	339
80°	253
85°	252

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1116 cd/sqm

TEST NUMBER: P1263828

CATALOG NUMBER: P3AS02R259730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.0	24.1
10°-20°	44.1	39.4
20°-30°	25.2	22.5
30°-40°	10.0	8.9
40°-50°	3.0	2.7
50°-60°	1.2	1.1
60°-70°	0.8	0.7
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.4	86.1
0°-40°	106.4	95.0
0°-60°	110.6	98.8
0°-90°	112.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	112.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	328	
5°	304	27
15°	161	44
25°	53	25
35°	15	10
45°	4	3
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1263828

CATALOG NUMBER: P3AS02R259730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	327.6
1°	327.0
2°	324.3
3°	319.6
4°	313.1
5°	304.5
6°	294.5
7°	283.1
8°	269.9
9°	256.5
10°	241.1
11°	226.1
12°	209.5
13°	193.1
14°	176.3
15°	160.6
17.5°	124.5
20°	94.5
22.5°	71.0
25°	53.3
27.5°	39.5
30°	29.0
32.5°	21.0
35°	15.1
37.5°	10.7
40°	7.5
42.5°	5.1
45°	3.6
47.5°	2.6
50°	1.9
52.5°	1.5
55°	1.3
57.5°	1.2
60°	1.0
62.5°	0.9
65°	0.9
67.5°	0.7
70°	0.6
72.5°	0.5
75°	0.4
77.5°	0.3
80°	0.2
82.5°	0.2
85°	0.1
87.5°	0.1



TEST NUMBER: P1263828

CATALOG NUMBER: P3AS02R259730DE010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)