

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263836

Luminaire Tested: P3AS02R259730DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263836
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259730DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 175.0 lumens
Efficiency: N/A
Efficacy: 48.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263836

CATALOG NUMBER: P3AS02R259730DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1263836

CATALOG NUMBER: P3AS02R259730DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70		
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59		
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55		
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51		
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48		
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41598
5°	40590
10°	37630
15°	33508
20°	28796
25°	24485
30°	20155
35°	15687
40°	11307
45°	7164
50°	4230
55°	2906
60°	2675
65°	2491
70°	2244
75°	2033
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7164 cd/sqm

TEST NUMBER: P1263836

CATALOG NUMBER: P3AS02R259730DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.1	9.8
10°-20°	41.0	23.4
20°-30°	46.3	26.5
30°-40°	36.6	20.9
40°-50°	18.5	10.6
50°-60°	7.4	4.2
60°-70°	4.7	2.7
70°-80°	2.6	1.5
80°-90°	0.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.4	59.6
0°-40°	141.0	80.6
0°-60°	166.9	95.4
0°-90°	175.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	175.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	190	
5°	184	17
15°	148	41
25°	101	46
35°	59	37
45°	23	18
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1263836

CATALOG NUMBER: P3AS02R259730DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	189.7
1°	189.7
2°	189.0
3°	187.9
4°	186.4
5°	184.4
6°	182.0
7°	179.2
8°	176.2
9°	172.7
10°	169.0
11°	164.8
12°	160.9
13°	156.3
14°	152.0
15°	147.6
17.5°	135.4
20°	123.4
22.5°	112.1
25°	101.2
27.5°	90.5
30°	79.6
32.5°	69.3
35°	58.6
37.5°	48.8
40°	39.5
42.5°	30.7
45°	23.1
47.5°	17.2
50°	12.4
52.5°	9.4
55°	7.6
57.5°	7.0
60°	6.1
62.5°	5.5
65°	4.8
67.5°	4.1
70°	3.5
72.5°	3.1
75°	2.4
77.5°	2.0
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.2



TEST NUMBER: P1263836

CATALOG NUMBER: P3AS02R259730DE010 E3DLD1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)