

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263031

Luminaire Tested: P3AS17R309727DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R309727DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1142.0 lumens
Efficiency: N/A
Efficacy: 53.9 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263031

CATALOG NUMBER: P3AS17R309727DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263031

CATALOG NUMBER: P3AS17R309727DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	666394
5°	634271
10°	533502
15°	384747
20°	238651
25°	135734
30°	75404
35°	41010
40°	21612
45°	11722
50°	6243
55°	4129
60°	3772
65°	3943
70°	3462
75°	2711
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11722 cd/sqm

TEST NUMBER: P1263031

CATALOG NUMBER: P3AS17R309727DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.5	22.7
10°-20°	461.2	40.4
20°-30°	266.6	23.3
30°-40°	101.2	8.9
40°-50°	31.1	2.7
50°-60°	10.4	0.9
60°-70°	7.1	0.6
70°-80°	3.8	0.3
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	987.2	86.4
0°-40°	1088.4	95.3
0°-60°	1129.9	98.9
0°-90°	1142.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1142.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3039	
5°	2882	259
15°	1695	461
25°	561	267
35°	153	101
45°	38	31
55°	11	10
65°	8	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1263031

CATALOG NUMBER: P3AS17R309727DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3039.0
1°	3036.8
2°	3018.5
3°	2984.0
4°	2940.8
5°	2881.5
6°	2806.0
7°	2721.8
8°	2628.0
9°	2515.8
10°	2396.0
11°	2266.6
12°	2129.6
13°	1986.1
14°	1840.4
15°	1694.8
17.5°	1336.6
20°	1022.7
22.5°	758.4
25°	561.0
27.5°	407.8
30°	297.8
32.5°	214.7
35°	153.2
37.5°	106.8
40°	75.5
42.5°	52.9
45°	37.8
47.5°	25.9
50°	18.3
52.5°	12.9
55°	10.8
57.5°	9.7
60°	8.6
62.5°	7.6
65°	7.6
67.5°	6.5
70°	5.4
72.5°	4.3
75°	3.2
77.5°	3.2
80°	2.2
82.5°	2.2
85°	1.1
87.5°	0.0



TEST NUMBER: P1263031
CATALOG NUMBER: P3AS17R309727DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)