

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263906

Luminaire Tested: P3AS02R359730DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263906
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359730DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 254.0 lumens
Efficiency: N/A
Efficacy: 70.6 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263906
CATALOG NUMBER: P3AS02R359730DE010 E3PH1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1263906
 CATALOG NUMBER: P3AS02R359730DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	94	93	92
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	91	90	89
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87	86	85
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85	84	83
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82	81	80
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80	79	78
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77	76	75
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75	74	73
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73	72	71

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	183494	183494	183494
5°	180343	179969	179573
10°	165283	160318	156421
15°	118366	114575	113190
20°	54885	56775	58758
25°	13017	18533	19332
30°	3823	4380	4937
35°	883	1419	1285
40°	200	372	258
45°	62	62	62
50°	68	0	68
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 52.5°
 Luminance: 72 cd/sqm



TEST NUMBER: P1263906
 CATALOG NUMBER: P3AS02R359730DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.1	29.6
10°-20°	134.3	52.9
20°-30°	40.4	15.9
30°-40°	3.9	1.5
40°-50°	0.3	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	249.9	98.4
0°-40°	253.7	99.9
0°-60°	254.0	100.0
0°-90°	254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	254.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	837	837	837	837	837	
5°	819	819	818	816	816	76
15°	521	517	505	502	499	138
25°	54	59	77	80	80	35
35°	3	4	5	6	5	3
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1263906

CATALOG NUMBER: P3AS02R359730DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	836.8	836.8	836.8	836.8	836.8
1°	836.4	836.4	836.0	836.0	835.1
2°	834.4	834.7	833.8	833.6	832.9
3°	831.4	830.7	830.7	830.3	829.8
4°	826.6	825.2	824.8	825.0	824.2
5°	819.3	819.1	817.6	816.5	815.8
6°	811.5	809.9	806.7	803.8	803.1
7°	799.6	796.4	793.5	787.6	786.7
8°	785.2	780.0	773.8	765.5	765.1
9°	767.5	759.0	750.4	739.3	735.3
10°	742.3	734.5	720.0	710.2	702.5
11°	711.0	701.2	684.4	672.5	666.2
12°	675.6	666.4	646.7	636.0	627.0
13°	630.1	622.4	604.1	592.2	585.2
14°	577.4	571.7	554.2	548.9	546.5
15°	521.4	517.4	504.7	502.5	498.6
17.5°	383.7	377.2	370.0	371.3	372.6
20°	235.2	244.4	243.3	248.1	251.8
22.5°	117.3	129.1	142.9	151.2	155.3
25°	53.8	59.3	76.6	79.9	79.9
27.5°	27.1	28.4	36.1	36.8	38.5
30°	15.1	16.2	17.3	19.3	19.5
32.5°	7.7	9.0	9.4	10.5	10.1
35°	3.3	4.4	5.3	5.7	4.8
37.5°	1.5	2.0	2.8	2.6	2.0
40°	0.7	0.9	1.3	1.1	0.9
42.5°	0.4	0.4	0.7	0.4	0.4
45°	0.2	0.2	0.2	0.2	0.2
47.5°	0.2	0.2	0.0	0.2	0.2
50°	0.2	0.0	0.0	0.0	0.2
52.5°	0.2	0.0	0.0	0.0	0.2
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1263906
CATALOG NUMBER: P3AS02R359730DE010 E3PH1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)