

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263068

Luminaire Tested: P3AS17R359727DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359727DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 699.0 lumens
Efficiency: N/A
Efficacy: 33.0 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263068
CATALOG NUMBER: P3AS17R359727DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1263068
 CATALOG NUMBER: P3AS17R359727DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	94	105	100	97	93	97	94	91	94	92	89	91	89	87	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	82	86	84	81	80			
4	97	89	83	79	95	88	82	78	86	81	77	84	80	77	82	78	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	77	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61			
8	79	70	64	60	78	69	63	59	68	63	59	67	62	59	66	62	59	57			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	224675
5°	219150
10°	200353
15°	170058
20°	134622
25°	101812
30°	74113
35°	50139
40°	30801
45°	17676
50°	10644
55°	8640
60°	7543
65°	6693
70°	5514
75°	5507
80°	5430
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17676 cd/sqm



TEST NUMBER: P1263068
 CATALOG NUMBER: P3AS17R359727DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	13.2
10°-20°	206.5	29.5
20°-30°	193.2	27.6
30°-40°	118.2	16.9
40°-50°	46.6	6.7
50°-60°	20.5	2.9
60°-70°	12.8	1.8
70°-80°	6.8	1.0
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	491.7	70.3
0°-40°	609.9	87.3
0°-60°	677.1	96.9
0°-90°	699.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	699.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1025	
5°	996	92
15°	749	207
25°	421	193
35°	187	118
45°	57	47
55°	23	21
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1263068
CATALOG NUMBER: P3AS17R359727DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1024.6
1°	1025.7
2°	1022.5
3°	1016.0
4°	1006.3
5°	995.6
6°	981.6
7°	965.4
8°	946.0
9°	924.5
10°	899.8
11°	873.9
12°	846.0
13°	815.8
14°	782.5
15°	749.1
17.5°	663.0
20°	576.9
22.5°	494.0
25°	420.8
27.5°	353.0
30°	292.7
32.5°	236.8
35°	187.3
37.5°	143.1
40°	107.6
42.5°	77.5
45°	57.0
47.5°	40.9
50°	31.2
52.5°	25.8
55°	22.6
57.5°	19.4
60°	17.2
62.5°	15.1
65°	12.9
67.5°	10.8
70°	8.6
72.5°	7.5
75°	6.5
77.5°	5.4
80°	4.3
82.5°	3.2
85°	2.2
87.5°	1.1



TEST NUMBER: P1263068
CATALOG NUMBER: P3AS17R359727DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)