

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263928

Luminaire Tested: P3AS02R409730DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409730DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 195.0 lumens
Efficiency: N/A
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263928
CATALOG NUMBER: P3AS02R409730DE010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1263928
 CATALOG NUMBER: P3AS02R409730DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43768
5°	42989
10°	40525
15°	36799
20°	32319
25°	27606
30°	22864
35°	17641
40°	12566
45°	8466
50°	4605
55°	3250
60°	3070
65°	2854
70°	2500
75°	2372
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8466 cd/sqm



TEST NUMBER: P1263928
 CATALOG NUMBER: P3AS02R409730DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.2	9.3
10°-20°	45.2	23.2
20°-30°	52.2	26.8
30°-40°	41.1	21.1
40°-50°	21.1	10.8
50°-60°	8.1	4.1
60°-70°	5.4	2.7
70°-80°	2.9	1.5
80°-90°	0.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.6	59.3
0°-40°	156.7	80.4
0°-60°	185.9	95.3
0°-90°	195.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	195.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	200	
5°	195	18
15°	162	45
25°	114	52
35°	66	41
45°	27	21
55°	8	8
65°	6	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1263928
CATALOG NUMBER: P3AS02R409730DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	199.6
2.5°	198.5
5°	195.3
7.5°	189.6
10°	182.0
12.5°	173.0
15°	162.1
17.5°	150.8
20°	138.5
22.5°	126.1
25°	114.1
27.5°	102.1
30°	90.3
32.5°	78.3
35°	65.9
37.5°	54.3
40°	43.9
42.5°	34.9
45°	27.3
47.5°	19.9
50°	13.5
52.5°	9.8
55°	8.5
57.5°	7.6
60°	7.0
62.5°	6.1
65°	5.5
67.5°	4.6
70°	3.9
72.5°	3.3
75°	2.8
77.5°	2.2
80°	1.5
82.5°	1.3
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)