

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263932

Luminaire Tested: P3AS02R409730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R409730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 78.9 lumens
Efficiency: N/A
Efficacy: 21.9 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263932

CATALOG NUMBER: P3AS02R409730DE010 E3DLP1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1263932

CATALOG NUMBER: P3AS02R409730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93		
2	107	102	98	95	105	101	97	94	97	94	91	94	92	90	92	89	88	86		
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	87	84	81	80		
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74		
5	92	83	78	73	90	82	77	73	81	76	72	79	75	72	77	74	71	69		
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	70	66	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24603
5°	24103
10°	22444
15°	19569
20°	15751
25°	11807
30°	8305
35°	5434
40°	3292
45°	1954
50°	1160
55°	956
60°	833
65°	726
70°	705
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1954 cd/sqm

TEST NUMBER: P1263932

CATALOG NUMBER: P3AS02R409730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	10.2	12.9
10°-20°	23.7	30.1
20°-30°	22.4	28.3
30°-40°	12.9	16.4
40°-50°	5.1	6.5
50°-60°	2.3	2.9
60°-70°	1.4	1.8
70°-80°	0.7	0.9
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	56.2	71.3
0°-40°	69.2	87.6
0°-60°	76.6	97.0
0°-90°	78.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	78.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	112	
5°	110	10
15°	86	24
25°	49	22
35°	20	13
45°	6	5
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263932

CATALOG NUMBER: P3AS02R409730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	112.2
2.5°	111.5
5°	109.5
7.5°	105.7
10°	100.8
12.5°	94.1
15°	86.2
17.5°	77.2
20°	67.5
22.5°	57.9
25°	48.8
27.5°	40.4
30°	32.8
32.5°	26.1
35°	20.3
37.5°	15.4
40°	11.5
42.5°	8.6
45°	6.3
47.5°	4.6
50°	3.4
52.5°	2.8
55°	2.5
57.5°	2.3
60°	1.9
62.5°	1.6
65°	1.4
67.5°	1.2
70°	1.1
72.5°	0.9
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)