

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263950

Luminaire Tested: P3AS02R459730DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R459730DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 244.0 lumens
Efficiency: N/A
Efficacy: 67.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263950

CATALOG NUMBER: P3AS02R459730DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263950

CATALOG NUMBER: P3AS02R459730DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	77	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	91637
5°	89478
10°	82252
15°	69694
20°	54068
25°	37793
30°	23801
35°	14027
40°	7929
45°	3845
50°	1330
55°	1070
60°	1053
65°	1038
70°	962
75°	932
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3845 cd/sqm

TEST NUMBER: P1263950

CATALOG NUMBER: P3AS02R459730DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	15.4
10°-20°	84.3	34.6
20°-30°	71.6	29.3
30°-40°	34.1	14.0
40°-50°	10.3	4.2
50°-60°	2.6	1.1
60°-70°	1.9	0.8
70°-80°	1.2	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.5	79.3
0°-40°	227.7	93.3
0°-60°	240.6	98.6
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	418	
5°	406	38
15°	307	84
25°	156	72
35°	52	34
45°	12	10
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1263950

CATALOG NUMBER: P3AS02R459730DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	417.9
2.5°	415.2
5°	406.5
7.5°	391.5
10°	369.4
12.5°	340.2
15°	307.0
17.5°	270.1
20°	231.7
22.5°	192.7
25°	156.2
27.5°	123.1
30°	94.0
32.5°	70.7
35°	52.4
37.5°	38.6
40°	27.7
42.5°	19.2
45°	12.4
47.5°	7.0
50°	3.9
52.5°	3.1
55°	2.8
57.5°	2.6
60°	2.4
62.5°	2.2
65°	2.0
67.5°	1.7
70°	1.5
72.5°	1.3
75°	1.1
77.5°	0.9
80°	0.7
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)