

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263245

Luminaire Tested: P3AS17R709727DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709727DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1348.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263245

CATALOG NUMBER: P3AS17R709727DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1263245

CATALOG NUMBER: P3AS17R709727DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	267676
5°	255425
10°	243015
15°	236528
20°	227776
25°	215577
30°	200512
35°	168432
40°	108546
45°	50455
50°	13236
55°	3288
60°	3289
65°	2802
70°	2757
75°	2711
80°	2778
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 50455 cd/sqm

TEST NUMBER: P1263245

CATALOG NUMBER: P3AS17R709727DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.6	8.1
10°-20°	292.7	21.7
20°-30°	409.0	30.3
30°-40°	379.2	28.1
40°-50°	136.0	10.1
50°-60°	11.5	0.9
60°-70°	5.7	0.4
70°-80°	3.7	0.3
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	810.4	60.1
0°-40°	1189.6	88.3
0°-60°	1337.1	99.2
0°-90°	1348.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1348.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1221	
5°	1160	109
15°	1042	293
25°	891	409
35°	629	379
45°	163	136
55°	9	11
65°	5	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1263245

CATALOG NUMBER: P3AS17R709727DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1220.7
2.5°	1202.4
5°	1160.4
7.5°	1121.6
10°	1091.4
12.5°	1066.6
15°	1041.9
17.5°	1011.7
20°	976.1
22.5°	935.2
25°	891.0
27.5°	845.8
30°	791.9
32.5°	722.9
35°	629.2
37.5°	509.6
40°	379.2
42.5°	258.6
45°	162.7
47.5°	90.5
50°	38.8
52.5°	12.9
55°	8.6
57.5°	7.5
60°	7.5
62.5°	6.5
65°	5.4
67.5°	5.4
70°	4.3
72.5°	4.3
75°	3.2
77.5°	3.2
80°	2.2
82.5°	2.2
85°	1.1
87.5°	1.1
90°	0.0

(END OF REPORT)