

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264032

Luminaire Tested: P3AS02R609730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 113.0 lumens
Efficiency: N/A
Efficacy: 31.4 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264032

CATALOG NUMBER: P3AS02R609730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264032

CATALOG NUMBER: P3AS02R609730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26686
5°	26436
10°	25651
15°	24041
20°	21282
25°	17807
30°	13952
35°	10119
40°	6727
45°	4186
50°	2286
55°	650
60°	614
65°	571
70°	577
75°	508
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4186 cd/sqm

TEST NUMBER: P1264032

CATALOG NUMBER: P3AS02R609730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	11.3	10.0
10°-20°	29.4	26.0
20°-30°	33.5	29.6
30°-40°	23.7	21.0
40°-50°	10.8	9.5
50°-60°	2.3	2.0
60°-70°	1.1	1.0
70°-80°	0.7	0.6
80°-90°	0.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	74.2	65.6
0°-40°	97.9	86.7
0°-60°	111.0	98.2
0°-90°	113.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	113.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	122	
5°	120	11
15°	106	29
25°	74	33
35°	38	24
45°	14	11
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264032

CATALOG NUMBER: P3AS02R609730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	121.7
2.5°	121.3
5°	120.1
7.5°	118.0
10°	115.2
12.5°	111.3
15°	105.9
17.5°	99.1
20°	91.2
22.5°	82.6
25°	73.6
27.5°	64.3
30°	55.1
32.5°	46.3
35°	37.8
37.5°	30.3
40°	23.5
42.5°	17.8
45°	13.5
47.5°	10.1
50°	6.7
52.5°	3.1
55°	1.7
57.5°	1.5
60°	1.4
62.5°	1.3
65°	1.1
67.5°	1.0
70°	0.9
72.5°	0.8
75°	0.6
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)