

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264034

Luminaire Tested: P3AS02R609730DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609730DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 229.9 lumens
Efficiency: N/A
Efficacy: 63.9 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264034

CATALOG NUMBER: P3AS02R609730DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1264034

CATALOG NUMBER: P3AS02R609730DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	54316
5°	53797
10°	52237
15°	48922
20°	43310
25°	36220
30°	28384
35°	20586
40°	13711
45°	8528
50°	4640
55°	1338
60°	1228
65°	1141
70°	1090
75°	1101
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8528 cd/sqm

TEST NUMBER: P1264034

CATALOG NUMBER: P3AS02R609730DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.0	10.0
10°-20°	59.8	26.0
20°-30°	68.1	29.6
30°-40°	48.3	21.0
40°-50°	21.9	9.5
50°-60°	4.7	2.0
60°-70°	2.2	1.0
70°-80°	1.4	0.6
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	151.0	65.7
0°-40°	199.3	86.7
0°-60°	225.9	98.2
0°-90°	229.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	229.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	248	
5°	244	23
15°	216	60
25°	150	68
35°	77	48
45°	28	22
55°	4	5
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264034

CATALOG NUMBER: P3AS02R609730DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	247.7
2.5°	246.8
5°	244.4
7.5°	240.2
10°	234.6
12.5°	226.5
15°	215.5
17.5°	201.8
20°	185.6
22.5°	168.1
25°	149.7
27.5°	130.9
30°	112.1
32.5°	94.2
35°	76.9
37.5°	61.6
40°	47.9
42.5°	36.3
45°	27.5
47.5°	20.5
50°	13.6
52.5°	6.3
55°	3.5
57.5°	3.1
60°	2.8
62.5°	2.6
65°	2.2
67.5°	2.0
70°	1.7
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)