

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263261

Luminaire Tested: P3AS17R709727DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R709727DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R70 optic, 2700K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1085.0 lumens
Efficiency: N/A
Efficacy: 51.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263261

CATALOG NUMBER: P3AS17R709727DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263261

CATALOG NUMBER: P3AS17R709727DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	210049
5°	207528
10°	201533
15°	192986
20°	180779
25°	164235
30°	141870
35°	113073
40°	82354
45°	54145
50°	25347
55°	7837
60°	7543
65°	7264
70°	6924
75°	7286
80°	6819
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 54145 cd/sqm

TEST NUMBER: P1263261

CATALOG NUMBER: P3AS17R709727DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	8.2
10°-20°	237.9	21.9
20°-30°	309.2	28.5
30°-40°	262.4	24.2
40°-50°	135.3	12.5
50°-60°	26.1	2.4
60°-70°	14.1	1.3
70°-80°	8.7	0.8
80°-90°	2.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	635.9	58.6
0°-40°	898.3	82.8
0°-60°	1059.7	97.7
0°-90°	1085.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1085.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	958	
5°	943	89
15°	850	238
25°	679	309
35°	422	262
45°	175	135
55°	20	26
65°	14	14
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P1263261

CATALOG NUMBER: P3AS17R709727DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	957.9
2.5°	954.7
5°	942.8
7.5°	925.6
10°	905.1
12.5°	879.2
15°	850.1
17.5°	814.6
20°	774.7
22.5°	729.5
25°	678.8
27.5°	621.7
30°	560.3
32.5°	492.4
35°	422.4
37.5°	353.4
40°	287.7
42.5°	226.3
45°	174.6
47.5°	128.2
50°	74.3
52.5°	32.3
55°	20.5
57.5°	19.4
60°	17.2
62.5°	16.2
65°	14.0
67.5°	12.9
70°	10.8
72.5°	9.7
75°	8.6
77.5°	6.5
80°	5.4
82.5°	3.2
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)