

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264044

Luminaire Tested: P3AS02R609730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 78.0 lumens
Efficiency: N/A
Efficacy: 21.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264044

CATALOG NUMBER: P3AS02R609730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264044

CATALOG NUMBER: P3AS02R609730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19757
5°	19326
10°	18103
15°	16232
20°	13955
25°	11541
30°	9115
35°	6773
40°	4666
45°	2915
50°	1603
55°	956
60°	833
65°	726
70°	641
75°	678
80°	505
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2915 cd/sqm

TEST NUMBER: P1264044

CATALOG NUMBER: P3AS02R609730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.2	10.5
10°-20°	19.9	25.5
20°-30°	21.8	27.9
30°-40°	15.9	20.3
40°-50°	7.5	9.6
50°-60°	2.4	3.1
60°-70°	1.4	1.8
70°-80°	0.8	1.0
80°-90°	0.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	49.8	63.9
0°-40°	65.7	84.2
0°-60°	75.6	96.9
0°-90°	78.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	78.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	90	
5°	88	8
15°	72	20
25°	48	22
35°	25	16
45°	9	7
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264044

CATALOG NUMBER: P3AS02R609730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	90.1
2.5°	89.6
5°	87.8
7.5°	85.0
10°	81.3
12.5°	76.7
15°	71.5
17.5°	65.8
20°	59.8
22.5°	53.7
25°	47.7
27.5°	41.7
30°	36.0
32.5°	30.5
35°	25.3
37.5°	20.6
40°	16.3
42.5°	12.5
45°	9.4
47.5°	6.9
50°	4.7
52.5°	3.1
55°	2.5
57.5°	2.1
60°	1.9
62.5°	1.6
65°	1.4
67.5°	1.2
70°	1.0
72.5°	0.9
75°	0.8
77.5°	0.5
80°	0.4
82.5°	0.3
85°	0.2
87.5°	0.1
90°	0.0

(END OF REPORT)