

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264072

Luminaire Tested: P3AS02R659730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264072
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R659730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 172.0 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264072

CATALOG NUMBER: P3AS02R659730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1264072

CATALOG NUMBER: P3AS02R659730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30612
5°	30200
10°	29191
15°	27514
20°	25389
25°	23034
30°	20408
35°	17373
40°	13826
45°	9768
50°	5663
55°	3097
60°	2895
65°	2594
70°	2372
75°	2203
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9768 cd/sqm

TEST NUMBER: P1264072

CATALOG NUMBER: P3AS02R659730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	12.9	7.5
10°-20°	33.9	19.7
20°-30°	43.6	25.3
30°-40°	40.3	23.4
40°-50°	24.4	14.2
50°-60°	8.3	4.8
60°-70°	5.0	2.9
70°-80°	2.8	1.6
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	90.4	52.5
0°-40°	130.7	76.0
0°-60°	163.4	95.0
0°-90°	172.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	172.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	140	
5°	137	13
15°	121	34
25°	95	44
35°	65	40
45°	32	24
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1264072

CATALOG NUMBER: P3AS02R659730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	139.6
2.5°	138.9
5°	137.2
7.5°	134.6
10°	131.1
12.5°	126.7
15°	121.2
17.5°	115.3
20°	108.8
22.5°	102.0
25°	95.2
27.5°	88.0
30°	80.6
32.5°	73.2
35°	64.9
37.5°	56.8
40°	48.3
42.5°	39.8
45°	31.5
47.5°	23.8
50°	16.6
52.5°	10.5
55°	8.1
57.5°	7.2
60°	6.6
62.5°	5.7
65°	5.0
67.5°	4.4
70°	3.7
72.5°	3.3
75°	2.6
77.5°	2.2
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)