

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263331

Luminaire Tested: P3AS20R159727D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159727D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R15 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 872.0 lumens
Efficiency: N/A
Efficacy: 30.3 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263331
CATALOG NUMBER: P3AS20R159727D010 E3DLP1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1263331
 CATALOG NUMBER: P3AS20R159727D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	106	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	108	103	98	95	105	101	97	94	98	95	92	95	92	90	92	90	88	86	86	86	86
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80	80	80	80
4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75
5	93	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70	70	70	70
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66	66	66	66
7	84	75	69	65	83	74	69	65	73	68	64	72	67	64	71	67	64	62	62	62	62
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59	59	59	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56	56	56	56
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	57	54	53	53	53	53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	376023
5°	347545
10°	277461
15°	209604
20°	159591
25°	121628
30°	87127
35°	56858
40°	34865
45°	21087
50°	14021
55°	10819
60°	9298
65°	8094
70°	7245
75°	7202
80°	5304
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21087 cd/sqm



TEST NUMBER: P1263331
 CATALOG NUMBER: P3AS20R159727D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.9	16.0
10°-20°	258.1	29.6
20°-30°	229.8	26.3
30°-40°	135.9	15.6
40°-50°	55.8	6.4
50°-60°	26.2	3.0
60°-70°	15.9	1.8
70°-80°	8.4	1.0
80°-90°	2.1	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	627.7	72.0
0°-40°	763.6	87.6
0°-60°	845.6	97.0
0°-90°	872.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	872.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1715	
5°	1579	140
15°	923	258
25°	503	230
35°	212	136
45°	68	56
55°	28	26
65°	16	16
75°	8	8
85°	1	2
90°	0	



TEST NUMBER: P1263331
CATALOG NUMBER: P3AS20R159727D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1714.8
1°	1710.6
2°	1697.8
3°	1672.3
4°	1629.9
5°	1578.9
6°	1523.7
7°	1458.5
8°	1390.5
9°	1321.2
10°	1246.1
12.5°	1074.8
15°	923.3
17.5°	793.0
20°	683.9
22.5°	587.7
25°	502.7
27.5°	420.6
30°	344.1
32.5°	274.7
35°	212.4
37.5°	162.8
40°	121.8
42.5°	90.6
45°	68.0
47.5°	52.4
50°	41.1
52.5°	34.0
55°	28.3
57.5°	24.1
60°	21.2
62.5°	18.4
65°	15.6
67.5°	14.2
70°	11.3
72.5°	9.9
75°	8.5
77.5°	5.7
80°	4.2
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)