

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263349

Luminaire Tested: P3AS20R209727D010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1263349  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R209727D010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 2700K CCT AND, 97CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1465.0 lumens  
Efficiency: N/A  
Efficacy: 50.9 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 28.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1263349  
CATALOG NUMBER: P3AS20R209727D010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1263349  
 CATALOG NUMBER: P3AS20R209727D010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1127147
5°	1024607
10°	757256
15°	468425
20°	267517
25°	152718
30°	85633
35°	46605
40°	25534
45°	14048
50°	8221
55°	5964
60°	5570
65°	5137
70°	4552
75°	4829
80°	3536
85°	3522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14048 cd/sqm



TEST NUMBER: P1263349  
 CATALOG NUMBER: P3AS20R209727D010 E3DL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	403.1	27.5
10°-20°	575.4	39.3
20°-30°	300.3	20.5
30°-40°	116.1	7.9
40°-50°	37.7	2.6
50°-60°	14.8	1.0
60°-70°	9.8	0.7
70°-80°	5.8	0.4
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1278.8	87.3
0°-40°	1395.0	95.2
0°-60°	1447.5	98.8
0°-90°	1465.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1465.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5140	
5°	4655	403
15°	2063	575
25°	631	300
35°	174	116
45°	45	38
55°	16	15
65°	10	10
75°	6	6
85°	1	2
90°	0	



TEST NUMBER: P1263349  
CATALOG NUMBER: P3AS20R209727D010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5140.2
1°	5130.3
2°	5069.5
3°	4976.0
4°	4831.7
5°	4654.8
6°	4445.3
7°	4213.2
8°	3944.3
9°	3682.5
10°	3400.9
12.5°	2703.1
15°	2063.4
17.5°	1544.0
20°	1146.4
22.5°	849.2
25°	631.2
27.5°	465.6
30°	338.2
32.5°	244.8
35°	174.1
37.5°	126.0
40°	89.2
42.5°	63.7
45°	45.3
47.5°	32.6
50°	24.1
52.5°	18.4
55°	15.6
57.5°	14.2
60°	12.7
62.5°	11.3
65°	9.9
67.5°	8.5
70°	7.1
72.5°	7.1
75°	5.7
77.5°	4.2
80°	2.8
82.5°	2.8
85°	1.4
87.5°	1.4
90°	0.0

(END OF REPORT)