

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263414

Luminaire Tested: P3AS20R309727D010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263414
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309727D010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 2700K CCT AND, 97CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1153.0 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263414

CATALOG NUMBER: P3AS20R309727D010 E3DLD1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1263414

CATALOG NUMBER: P3AS20R309727D010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	85	79	74	92	84	79	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	272390
5°	266277
10°	247624
15°	220342
20°	189506
25°	160558
30°	133261
35°	104534
40°	74912
45°	49152
50°	28008
55°	18389
60°	17367
65°	16137
70°	14490
75°	13217
80°	12502
85°	10567

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 49152 cd/sqm

TEST NUMBER: P1263414

CATALOG NUMBER: P3AS20R309727D010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.3	9.7
10°-20°	269.8	23.4
20°-30°	304.1	26.4
30°-40°	242.8	21.1
40°-50°	124.8	10.8
50°-60°	47.0	4.1
60°-70°	30.8	2.7
70°-80°	16.6	1.4
80°-90°	4.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	686.2	59.5
0°-40°	929.0	80.6
0°-60°	1100.8	95.5
0°-90°	1153.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1153.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1242	
5°	1210	112
15°	971	270
25°	664	304
35°	390	243
45°	158	125
55°	48	47
65°	31	31
75°	16	17
85°	4	5
90°	0	

TEST NUMBER: P1263414

CATALOG NUMBER: P3AS20R309727D010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1242.2
1°	1242.2
2°	1238.0
3°	1230.9
4°	1221.0
5°	1209.7
6°	1195.5
7°	1177.2
8°	1157.3
9°	1134.7
10°	1112.1
11°	1086.6
12°	1059.7
13°	1031.4
14°	1001.7
15°	970.6
17.5°	891.4
20°	812.1
22.5°	735.7
25°	663.6
27.5°	592.8
30°	526.3
32.5°	458.4
35°	390.5
37.5°	324.0
40°	261.7
42.5°	206.6
45°	158.5
47.5°	117.4
50°	82.1
52.5°	58.0
55°	48.1
57.5°	43.9
60°	39.6
62.5°	35.4
65°	31.1
67.5°	26.9
70°	22.6
72.5°	18.4
75°	15.6
77.5°	12.7
80°	9.9
82.5°	7.1
85°	4.2
87.5°	1.4



TEST NUMBER: P1263414

CATALOG NUMBER: P3AS20R309727D010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)