

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264087

Luminaire Tested: P3AS02R709730DE010 E3D1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1264087  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS02R709730DE010 E3D1MW  
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 273.0 lumens  
Efficiency: N/A  
Efficacy: 75.8 lumens/watt  
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 3.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264087  
CATALOG NUMBER: P3AS02R709730DE010 E3D1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264087

CATALOG NUMBER: P3AS02R709730DE010 E3D1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	97	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	82	80	78			78
4	95	87	81	77	94	86	81	76	84	79	75	82	78	75	80	77	74	72			72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	59	55	75	65	59	55	64	58	55	63	58	54	62	57	54	53			53
9	72	62	55	51	71	61	55	51	60	55	51	59	54	50	58	54	50	49			49
10	68	58	52	47	67	57	51	47	56	51	47	56	51	47	55	50	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54206
5°	51728
10°	49209
15°	47900
20°	46134
25°	43672
30°	40614
35°	34104
40°	21984
45°	10203
50°	2695
55°	650
60°	658
65°	571
70°	577
75°	593
80°	505
85°	503

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10203 cd/sqm



TEST NUMBER: P1264087  
 CATALOG NUMBER: P3AS02R709730DE010 E3D1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	22.0	8.1
10°-20°	59.3	21.7
20°-30°	82.8	30.3
30°-40°	76.8	28.1
40°-50°	27.5	10.1
50°-60°	2.3	0.8
60°-70°	1.2	0.4
70°-80°	0.8	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	164.1	60.1
0°-40°	240.9	88.3
0°-60°	270.8	99.2
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	247	
5°	235	22
15°	211	59
25°	180	83
35°	127	77
45°	33	28
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264087  
CATALOG NUMBER: P3AS02R709730DE010 E3D1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	247.2
2.5°	243.5
5°	235.0
7.5°	227.1
10°	221.0
12.5°	216.0
15°	211.0
17.5°	204.9
20°	197.7
22.5°	189.4
25°	180.5
27.5°	171.3
30°	160.4
32.5°	146.4
35°	127.4
37.5°	103.2
40°	76.8
42.5°	52.4
45°	32.9
47.5°	18.3
50°	7.9
52.5°	2.6
55°	1.7
57.5°	1.5
60°	1.5
62.5°	1.3
65°	1.1
67.5°	1.1
70°	0.9
72.5°	0.9
75°	0.7
77.5°	0.7
80°	0.4
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)