

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264098

Luminaire Tested: P3AS02R709730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 157.0 lumens
Efficiency: N/A
Efficacy: 43.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264098
CATALOG NUMBER: P3AS02R709730DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264098
 CATALOG NUMBER: P3AS02R709730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	36817
5°	36143
10°	34090
15°	30942
20°	27069
25°	22816
30°	18686
35°	14509
40°	10391
45°	6574
50°	3275
55°	1988
60°	1710
65°	1608
70°	1410
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6574 cd/sqm



TEST NUMBER: P1264098
 CATALOG NUMBER: P3AS02R709730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.3	9.8
10°-20°	37.9	24.1
20°-30°	43.2	27.5
30°-40°	33.8	21.5
40°-50°	16.6	10.6
50°-60°	5.1	3.2
60°-70°	3.0	1.9
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	96.4	61.4
0°-40°	130.2	82.9
0°-60°	151.9	96.8
0°-90°	157.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	157.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	168	
5°	164	15
15°	136	38
25°	94	43
35°	54	34
45°	21	17
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1264098
CATALOG NUMBER: P3AS02R709730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	167.9
2.5°	167.1
5°	164.2
7.5°	159.6
10°	153.1
12.5°	145.4
15°	136.3
17.5°	126.4
20°	116.0
22.5°	105.0
25°	94.3
27.5°	83.9
30°	73.8
32.5°	63.8
35°	54.2
37.5°	45.0
40°	36.3
42.5°	28.2
45°	21.2
47.5°	14.9
50°	9.6
52.5°	6.3
55°	5.2
57.5°	4.6
60°	3.9
62.5°	3.5
65°	3.1
67.5°	2.6
70°	2.2
72.5°	1.7
75°	1.5
77.5°	1.3
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)