

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263429

Luminaire Tested: P3AS20R359727D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359727D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1797.0 lumens
Efficiency: N/A
Efficacy: 62.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263429

CATALOG NUMBER: P3AS20R359727D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1263429

CATALOG NUMBER: P3AS20R359727D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1171770
5°	1147895
10°	1067894
15°	782933
20°	400902
25°	144492
30°	56262
35°	19702
40°	8101
45°	2202
50°	1944
55°	2179
60°	1842
65°	1453
70°	1795
75°	2372
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 75°
Luminance: 2372 cd/sqm

TEST NUMBER: P1263429

CATALOG NUMBER: P3AS20R359727D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	486.2	27.1
10°-20°	912.2	50.8
20°-30°	322.9	18.0
30°-40°	56.6	3.1
40°-50°	8.3	0.5
50°-60°	4.6	0.3
60°-70°	3.3	0.2
70°-80°	2.4	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1721.3	95.8
0°-40°	1777.8	98.9
0°-60°	1790.7	99.7
0°-90°	1797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5344	
5°	5215	486
15°	3449	912
25°	597	323
35°	74	57
45°	7	8
55°	6	5
65°	3	3
75°	3	2
85°	0	1
90°	0	

TEST NUMBER: P1263429

CATALOG NUMBER: P3AS20R359727D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	5343.7
1°	5342.3
2°	5325.3
3°	5292.7
4°	5263.0
5°	5214.9
6°	5165.4
7°	5110.2
8°	5042.2
9°	4936.1
10°	4796.0
11°	4602.1
12°	4368.6
13°	4091.2
14°	3785.6
15°	3448.8
17.5°	2568.5
20°	1718.0
22.5°	1035.9
25°	597.2
27.5°	356.6
30°	222.2
32.5°	128.8
35°	73.6
37.5°	46.7
40°	28.3
42.5°	14.2
45°	7.1
47.5°	5.7
50°	5.7
52.5°	5.7
55°	5.7
57.5°	4.2
60°	4.2
62.5°	4.2
65°	2.8
67.5°	2.8
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0



TEST NUMBER: P1263429

CATALOG NUMBER: P3AS20R359727D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)