

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263449

Luminaire Tested: P3AS20R359727D010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263449
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R359727D010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 2700K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 918.0 lumens
Efficiency: N/A
Efficacy: 31.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.72
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263449

CATALOG NUMBER: P3AS20R359727D010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1263449

CATALOG NUMBER: P3AS20R359727D010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	97	93	97	94	91		94	92	89		91
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86
4	97	89	83	79	95	88	82	78	86	81	77		84	80	77		82
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77
6	87	78	72	68	86	77	72	68	76	71	67		75	70	67		73
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	70	64	60	78	69	63	59	68	63	59		67	62	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295064
5°	287805
10°	263121
15°	223338
20°	176789
25°	133725
30°	97357
35°	65826
40°	40447
45°	23227
50°	13987
55°	11354
60°	9911
65°	8821
70°	7245
75°	7202
80°	7198
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23227 cd/sqm

TEST NUMBER: P1263449

CATALOG NUMBER: P3AS20R359727D010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.8	13.2
10°-20°	271.2	29.5
20°-30°	253.7	27.6
30°-40°	155.3	16.9
40°-50°	61.2	6.7
50°-60°	26.9	2.9
60°-70°	16.8	1.8
70°-80°	9.0	1.0
80°-90°	3.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	645.8	70.3
0°-40°	801.0	87.3
0°-60°	889.2	96.9
0°-90°	918.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	918.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1346	
5°	1308	121
15°	984	271
25°	553	254
35°	246	155
45°	75	61
55°	30	27
65°	17	17
75°	8	9
85°	3	3
90°	0	

TEST NUMBER: P1263449

CATALOG NUMBER: P3AS20R359727D010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1345.6
1°	1347.0
2°	1342.8
3°	1334.3
4°	1321.6
5°	1307.5
6°	1289.1
7°	1267.9
8°	1242.4
9°	1214.2
10°	1181.7
11°	1147.7
12°	1111.0
13°	1071.4
14°	1027.6
15°	983.8
17.5°	870.7
20°	757.6
22.5°	648.8
25°	552.7
27.5°	463.6
30°	384.5
32.5°	311.0
35°	245.9
37.5°	188.0
40°	141.3
42.5°	101.8
45°	74.9
47.5°	53.7
50°	41.0
52.5°	33.9
55°	29.7
57.5°	25.4
60°	22.6
62.5°	19.8
65°	17.0
67.5°	14.1
70°	11.3
72.5°	9.9
75°	8.5
77.5°	7.1
80°	5.7
82.5°	4.2
85°	2.8
87.5°	1.4



TEST NUMBER: P1263449

CATALOG NUMBER: P3AS20R359727D010 E3DLP1WMH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)