

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264200

Luminaire Tested: P3AS05R159730DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1264200  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R159730DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 296.0 lumens  
Efficiency: N/A  
Efficacy: 41.1 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.67  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264200  
CATALOG NUMBER: P3AS05R159730DE010 E3PHLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264200  
 CATALOG NUMBER: P3AS05R159730DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	95	93	92	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	87	85	82	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	81	77	74	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	70	65	62	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	65	60	57	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	61	56	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	58	53	49	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	54	49	46	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	86133
5°	80739
10°	66220
15°	51442
20°	40604
25°	32373
30°	25979
35°	21201
40°	17461
45°	14699
50°	12622
55°	10934
60°	9692
65°	8406
70°	7501
75°	6015
80°	4925
85°	3271

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14699 cd/sqm



TEST NUMBER: P1264200  
 CATALOG NUMBER: P3AS05R159730DE010 E3PHLD1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	32.8	11.1
10°-20°	63.5	21.4
20°-30°	61.7	20.8
30°-40°	49.9	16.8
40°-50°	37.0	12.5
50°-60°	25.9	8.7
60°-70°	16.2	5.5
70°-80°	7.7	2.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	157.9	53.4
0°-40°	207.8	70.2
0°-60°	270.7	91.5
0°-90°	296.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	296.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	393	
5°	367	33
15°	227	63
25°	134	62
35°	79	50
45°	47	37
55°	29	26
65°	16	16
75°	7	8
85°	1	1
90°	0	

TEST NUMBER: P1264200

CATALOG NUMBER: P3AS05R159730DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	392.8
2.5°	386.3
5°	366.8
7.5°	335.7
10°	297.4
12.5°	259.7
15°	226.6
17.5°	198.7
20°	174.0
22.5°	152.6
25°	133.8
27.5°	116.9
30°	102.6
32.5°	90.3
35°	79.2
37.5°	69.5
40°	61.0
42.5°	53.9
45°	47.4
47.5°	42.2
50°	37.0
52.5°	32.5
55°	28.6
57.5°	25.3
60°	22.1
62.5°	18.8
65°	16.2
67.5°	13.6
70°	11.7
72.5°	9.1
75°	7.1
77.5°	5.2
80°	3.9
82.5°	1.9
85°	1.3
87.5°	0.0
90°	0.0

(END OF REPORT)