

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264209

Luminaire Tested: P3AS05R209730DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264209
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209730DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 563.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264209
CATALOG NUMBER: P3AS05R209730DE010 E3D1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1264209

CATALOG NUMBER: P3AS05R209730DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99		97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96		95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94		93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92		91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90		89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88		87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86		85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84		83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82		81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81		80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	854032
5°	719060
10°	449112
15°	167901
20°	57638
25°	24026
30°	11318
35°	5059
40°	2405
45°	1240
50°	443
55°	76
60°	88
65°	104
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1240 cd/sqm



TEST NUMBER: P1264209

CATALOG NUMBER: P3AS05R209730DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.7	48.3
10°-20°	223.8	39.7
20°-30°	50.8	9.0
30°-40°	12.9	2.3
40°-50°	3.2	0.6
50°-60°	0.4	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.3	97.0
0°-40°	559.2	99.3
0°-60°	562.9	100.0
0°-90°	563.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	563.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3895	
5°	3267	272
15°	740	224
25°	99	51
35°	19	13
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1264209
CATALOG NUMBER: P3AS05R209730DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3894.7
1°	3861.6
2°	3764.4
3°	3624.8
4°	3453.5
5°	3266.7
6°	3058.4
7°	2828.6
8°	2560.5
9°	2294.8
10°	2017.0
11°	1721.4
12°	1426.2
13°	1176.1
14°	937.1
15°	739.6
16°	583.8
17°	460.5
18°	370.0
19°	300.9
20°	247.0
21°	206.5
22°	172.4
23°	143.3
24°	119.5
25°	99.3
27.5°	64.9
30°	44.7
32.5°	27.5
35°	18.9
37.5°	12.1
40°	8.4
42.5°	5.7
45°	4.0
47.5°	2.6
50°	1.3
52.5°	0.7
55°	0.2
57.5°	0.2
60°	0.2
62.5°	0.2
65°	0.2
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1264209
CATALOG NUMBER: P3AS05R209730DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)