

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264210

Luminaire Tested: P3AS05R209730DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264210
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R209730DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 566.9 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264210
CATALOG NUMBER: P3AS05R209730DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1264210
 CATALOG NUMBER: P3AS05R209730DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	97	97
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	95	95
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	92	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	91	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	89	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	87	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	84	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	82	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	880609
5°	764339
10°	472291
15°	164042
20°	50381
25°	17807
30°	6583
35°	2650
40°	1403
45°	558
50°	307
55°	344
60°	395
65°	208
70°	256
75°	339
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 558 cd/sqm



TEST NUMBER: P1264210
 CATALOG NUMBER: P3AS05R209730DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	288.2	50.8
10°-20°	228.7	40.3
20°-30°	39.6	7.0
30°-40°	7.2	1.3
40°-50°	1.6	0.3
50°-60°	0.8	0.1
60°-70°	0.5	0.1
70°-80°	0.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.4	98.2
0°-40°	563.6	99.4
0°-60°	566.1	99.9
0°-90°	566.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	566.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4016	
5°	3472	288
15°	723	229
25°	74	40
35°	10	7
45°	2	2
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1264210
CATALOG NUMBER: P3AS05R209730DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4015.9
1°	3996.6
2°	3920.3
3°	3797.8
4°	3654.2
5°	3472.4
6°	3264.2
7°	3021.8
8°	2745.8
9°	2435.7
10°	2121.1
12.5°	1337.9
15°	722.6
17.5°	386.0
20°	215.9
22.5°	123.4
25°	73.6
27.5°	44.9
30°	26.0
32.5°	15.3
35°	9.9
37.5°	6.7
40°	4.9
42.5°	3.1
45°	1.8
47.5°	0.9
50°	0.9
52.5°	0.9
55°	0.9
57.5°	0.9
60°	0.9
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.4
75°	0.4
77.5°	0.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)