

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263524

Luminaire Tested: P3AS20R509727D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263524
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509727D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 2700K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 608.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263524

CATALOG NUMBER: P3AS20R509727D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1263524

CATALOG NUMBER: P3AS20R509727D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123565
5°	121747
10°	116342
15°	107742
20°	96842
25°	85118
30°	72391
35°	58705
40°	44111
45°	28406
50°	13509
55°	10628
60°	10043
65°	9340
70°	8463
75°	7625
80°	7072
85°	7045

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 28406 cd/sqm

TEST NUMBER: P1263524

CATALOG NUMBER: P3AS20R509727D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	8.5
10°-20°	132.3	21.8
20°-30°	160.8	26.4
30°-40°	136.4	22.4
40°-50°	70.8	11.7
50°-60°	25.6	4.2
60°-70°	17.7	2.9
70°-80°	9.6	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.9	56.7
0°-40°	481.3	79.2
0°-60°	577.7	95.0
0°-90°	608.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	608.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	564	
5°	553	52
15°	475	132
25°	352	161
35°	219	136
45°	92	71
55°	28	26
65°	18	18
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1263524

CATALOG NUMBER: P3AS20R509727D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	563.5
2.5°	561.4
5°	553.1
7.5°	540.6
10°	522.5
12.5°	499.6
15°	474.6
17.5°	446.2
20°	415.0
22.5°	383.0
25°	351.8
27.5°	319.2
30°	285.9
32.5°	252.6
35°	219.3
37.5°	186.7
40°	154.1
42.5°	122.8
45°	91.6
47.5°	61.1
50°	39.6
52.5°	30.5
55°	27.8
57.5°	25.0
60°	22.9
62.5°	20.1
65°	18.0
67.5°	15.3
70°	13.2
72.5°	11.1
75°	9.0
77.5°	6.9
80°	5.6
82.5°	4.2
85°	2.8
87.5°	1.4
90°	0.0

(END OF REPORT)