

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264226

Luminaire Tested: P3AS05R209730DE010 E3PHLD1MW

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1264226  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R209730DE010 E3PHLD1MW  
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 309.0 lumens  
Efficiency: N/A  
Efficacy: 42.9 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1264226

CATALOG NUMBER: P3AS05R209730DE010 E3PHLD1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1264226

CATALOG NUMBER: P3AS05R209730DE010 E3PHLD1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97  |  | 98  | 96  | 95  |  | 95  |
| 2   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 93  | 89  | 86  |  | 90  | 87  | 84  |  | 87  |
| 3   | 98  | 90  | 83  | 78  | 95  | 88  | 82  | 78  | 85  | 81  | 77  |  | 83  | 79  | 75  |  | 80  |
| 4   | 92  | 82  | 75  | 70  | 90  | 81  | 75  | 70  | 79  | 73  | 69  |  | 77  | 72  | 68  |  | 75  |
| 5   | 86  | 76  | 69  | 64  | 84  | 75  | 68  | 63  | 73  | 67  | 63  |  | 71  | 66  | 62  |  | 70  |
| 6   | 81  | 70  | 63  | 58  | 79  | 70  | 63  | 58  | 68  | 62  | 58  |  | 66  | 61  | 57  |  | 65  |
| 7   | 76  | 66  | 59  | 54  | 75  | 65  | 58  | 53  | 64  | 58  | 53  |  | 62  | 57  | 53  |  | 61  |
| 8   | 72  | 61  | 54  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  |  | 58  | 53  | 49  |  | 57  |
| 9   | 69  | 58  | 51  | 46  | 67  | 57  | 51  | 46  | 56  | 50  | 46  |  | 55  | 50  | 46  |  | 54  |
| 10  | 65  | 54  | 48  | 43  | 64  | 54  | 48  | 43  | 53  | 47  | 43  |  | 52  | 47  | 43  |  | 51  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 87625 |
| 5°  | 81400 |
| 10° | 68937 |
| 15° | 53962 |
| 20° | 42470 |
| 25° | 33849 |
| 30° | 27219 |
| 35° | 22192 |
| 40° | 18349 |
| 45° | 15474 |
| 50° | 13270 |
| 55° | 11393 |
| 60° | 9955  |
| 65° | 8717  |
| 70° | 7501  |
| 75° | 6608  |
| 80° | 4925  |
| 85° | 3271  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15474 cd/sqm

TEST NUMBER: P1264226

CATALOG NUMBER: P3AS05R209730DE010 E3PHLD1MW

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 33.4   | 10.8      |
| 10°-20°   | 66.5   | 21.5      |
| 20°-30°   | 64.6   | 20.9      |
| 30°-40°   | 52.2   | 16.9      |
| 40°-50°   | 38.8   | 12.6      |
| 50°-60°   | 27.0   | 8.7       |
| 60°-70°   | 16.9   | 5.5       |
| 70°-80°   | 8.2    | 2.7       |
| 80°-90°   | 1.4    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 164.6  | 53.3      |
| 0°-40°    | 216.8  | 70.2      |
| 0°-60°    | 282.5  | 91.4      |
| 0°-90°    | 309.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 309.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 400 |      |
| 5°  | 370 | 33   |
| 15° | 238 | 67   |
| 25° | 140 | 65   |
| 35° | 83  | 52   |
| 45° | 50  | 39   |
| 55° | 30  | 27   |
| 65° | 17  | 17   |
| 75° | 8   | 8    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1264226

CATALOG NUMBER: P3AS05R209730DE010 E3PHLD1MW

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 399.6 |
| 2.5°  | 390.6 |
| 5°    | 369.8 |
| 7.5°  | 342.0 |
| 10°   | 309.6 |
| 12.5° | 274.0 |
| 15°   | 237.7 |
| 17.5° | 207.9 |
| 20°   | 182.0 |
| 22.5° | 159.3 |
| 25°   | 139.9 |
| 27.5° | 123.1 |
| 30°   | 107.5 |
| 32.5° | 94.6  |
| 35°   | 82.9  |
| 37.5° | 72.5  |
| 40°   | 64.1  |
| 42.5° | 56.4  |
| 45°   | 49.9  |
| 47.5° | 44.0  |
| 50°   | 38.9  |
| 52.5° | 34.3  |
| 55°   | 29.8  |
| 57.5° | 25.9  |
| 60°   | 22.7  |
| 62.5° | 20.1  |
| 65°   | 16.8  |
| 67.5° | 14.2  |
| 70°   | 11.7  |
| 72.5° | 9.7   |
| 75°   | 7.8   |
| 77.5° | 5.8   |
| 80°   | 3.9   |
| 82.5° | 1.9   |
| 85°   | 1.3   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)