

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264305

Luminaire Tested: P3AS05R359730DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R359730DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 178.0 lumens
Efficiency: N/A
Efficacy: 24.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264305

CATALOG NUMBER: P3AS05R359730DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264305

CATALOG NUMBER: P3AS05R359730DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	40655
5°	39797
10°	37274
15°	33462
20°	29099
25°	24800
30°	20763
35°	16543
40°	11965
45°	7567
50°	4128
55°	2867
60°	2719
65°	2491
70°	2372
75°	2033
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7567 cd/sqm

TEST NUMBER: P1264305

CATALOG NUMBER: P3AS05R359730DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.8	9.5
10°-20°	41.0	23.0
20°-30°	47.0	26.4
30°-40°	38.3	21.5
40°-50°	19.3	10.9
50°-60°	7.2	4.0
60°-70°	4.8	2.7
70°-80°	2.7	1.5
80°-90°	0.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.8	58.9
0°-40°	143.2	80.4
0°-60°	169.7	95.4
0°-90°	178.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	178.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	185	
5°	181	17
15°	147	41
25°	102	47
35°	62	38
45°	24	19
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1264305

CATALOG NUMBER: P3AS05R359730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	185.4
1°	185.2
2°	184.8
3°	183.9
4°	182.6
5°	180.8
6°	178.6
7°	176.4
8°	173.5
9°	170.7
10°	167.4
11°	163.9
12°	160.1
13°	156.0
14°	151.6
15°	147.4
17.5°	136.2
20°	124.7
22.5°	113.1
25°	102.5
27.5°	92.2
30°	82.0
32.5°	71.9
35°	61.8
37.5°	51.7
40°	41.8
42.5°	32.6
45°	24.4
47.5°	17.6
50°	12.1
52.5°	8.8
55°	7.5
57.5°	6.8
60°	6.2
62.5°	5.5
65°	4.8
67.5°	4.2
70°	3.7
72.5°	3.1
75°	2.4
77.5°	2.0
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4



TEST NUMBER: P1264305

CATALOG NUMBER: P3AS05R359730DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)