

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264350

Luminaire Tested: P3AS05R459730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264350
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 601.9 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264350

CATALOG NUMBER: P3AS05R459730DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1264350

CATALOG NUMBER: P3AS05R459730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		95
2	110	106	102	100	108	104	101	98	101	98	96		98	96	94		91
3	106	100	96	93	104	99	95	92	96	93	91		94	91	89		87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		83
5	98	91	86	82	96	90	85	82	88	84	81		87	83	81		79
6	94	87	82	78	93	86	81	78	85	80	77		83	80	77		75
7	90	83	78	74	89	82	78	74	81	77	74		80	76	74		72
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		69
9	84	76	71	68	83	76	71	68	75	71	68		74	70	67		66
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	261010
5°	262403
10°	254326
15°	213123
20°	162927
25°	99175
30°	41272
35°	13224
40°	4122
45°	837
50°	614
55°	688
60°	570
65°	675
70°	577
75°	763
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 837 cd/sqm

TEST NUMBER: P1264350

CATALOG NUMBER: P3AS05R459730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	18.7
10°-20°	258.0	42.9
20°-30°	185.8	30.9
30°-40°	38.6	6.4
40°-50°	3.5	0.6
50°-60°	1.4	0.2
60°-70°	1.1	0.2
70°-80°	0.8	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	556.2	92.4
0°-40°	594.9	98.8
0°-60°	599.9	99.7
0°-90°	601.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1190	
5°	1192	112
15°	939	258
25°	410	186
35°	49	39
45°	3	4
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1264350

CATALOG NUMBER: P3AS05R459730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1190.3
2.5°	1190.7
5°	1192.1
7.5°	1183.5
10°	1142.2
12.5°	1056.0
15°	938.8
17.5°	818.9
20°	698.2
22.5°	559.4
25°	409.9
27.5°	270.3
30°	163.0
32.5°	91.1
35°	49.4
37.5°	27.8
40°	14.4
42.5°	6.3
45°	2.7
47.5°	1.8
50°	1.8
52.5°	1.8
55°	1.8
57.5°	1.3
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.9
70°	0.9
72.5°	0.9
75°	0.9
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)