

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1263724

Luminaire Tested: P3AS02R109730DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1263724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109730DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 154.0 lumens
Efficiency: N/A
Efficacy: 40.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1263724

CATALOG NUMBER: P3AS02R109730DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1263724

CATALOG NUMBER: P3AS02R109730DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	104	98	93	89	102	97	92	88	93	89	86		90	87	84		87
3	98	90	84	79	96	88	83	78	85	81	77		83	79	75		81
4	92	82	76	70	90	81	75	70	79	73	69		77	72	68		75
5	86	76	69	64	84	75	68	63	73	67	63		71	66	62		70
6	81	70	63	58	79	70	63	58	68	62	58		67	61	57		65
7	77	66	59	54	75	65	58	54	64	58	53		62	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	69	58	51	46	68	57	51	46	56	50	46		55	50	46		54
10	65	54	48	44	64	54	48	44	53	47	43		52	47	43		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44821
5°	42021
10°	34446
15°	26765
20°	21119
25°	16840
30°	13521
35°	11029
40°	9103
45°	7660
50°	6584
55°	5696
60°	5043
65°	4358
70°	3911
75°	3135
80°	2526
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7660 cd/sqm

TEST NUMBER: P1263724

CATALOG NUMBER: P3AS02R109730DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.0	11.1
10°-20°	33.0	21.4
20°-30°	32.1	20.8
30°-40°	25.9	16.8
40°-50°	19.3	12.5
50°-60°	13.5	8.8
60°-70°	8.4	5.5
70°-80°	4.0	2.6
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	82.2	53.3
0°-40°	108.1	70.2
0°-60°	140.9	91.5
0°-90°	154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	154.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	204	
5°	191	17
15°	118	33
25°	70	32
35°	41	26
45°	25	19
55°	15	13
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1263724

CATALOG NUMBER: P3AS02R109730DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	204.4
2.5°	201.0
5°	190.9
7.5°	174.6
10°	154.7
12.5°	135.1
15°	117.9
17.5°	103.4
20°	90.5
22.5°	79.4
25°	69.6
27.5°	60.8
30°	53.4
32.5°	47.0
35°	41.2
37.5°	36.1
40°	31.8
42.5°	28.0
45°	24.7
47.5°	22.0
50°	19.3
52.5°	16.9
55°	14.9
57.5°	13.2
60°	11.5
62.5°	9.8
65°	8.4
67.5°	7.1
70°	6.1
72.5°	4.7
75°	3.7
77.5°	2.7
80°	2.0
82.5°	1.0
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)