

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1264368

Luminaire Tested: P3AS05R459730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1264368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R459730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 159.0 lumens
Efficiency: N/A
Efficacy: 22.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1264368

CATALOG NUMBER: P3AS05R459730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1264368

CATALOG NUMBER: P3AS05R459730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47365
5°	46269
10°	42685
15°	37117
20°	30499
25°	23735
30°	17522
35°	12341
40°	7700
45°	4155
50°	2252
55°	1950
60°	1754
65°	1505
70°	1282
75°	1271
80°	1137
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4155 cd/sqm

TEST NUMBER: P1264368

CATALOG NUMBER: P3AS05R459730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	19.5	12.2
10°-20°	45.2	28.4
20°-30°	44.9	28.2
30°-40°	28.9	18.2
40°-50°	11.1	7.0
50°-60°	4.5	2.9
60°-70°	2.9	1.8
70°-80°	1.5	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	109.6	68.9
0°-40°	138.5	87.1
0°-60°	154.1	96.9
0°-90°	159.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	159.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	216	
5°	210	19
15°	164	45
25°	98	45
35°	46	29
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1264368

CATALOG NUMBER: P3AS05R459730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.0
2.5°	214.9
5°	210.2
7.5°	202.3
10°	191.7
12.5°	178.5
15°	163.5
17.5°	147.2
20°	130.7
22.5°	113.9
25°	98.1
27.5°	83.1
30°	69.2
32.5°	57.1
35°	46.1
37.5°	36.1
40°	26.9
42.5°	19.4
45°	13.4
47.5°	9.0
50°	6.6
52.5°	5.5
55°	5.1
57.5°	4.4
60°	4.0
62.5°	3.3
65°	2.9
67.5°	2.4
70°	2.0
72.5°	1.8
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)